

See the Difference - Compare These High Pressure Non-Spill Quick Couplings

59 Series

Premium performance and a unique interface

FET Series

Improved performance and field interchangeability



Features	Parker 59 Series	Parker FET Series	Similar Competitive Coupling
Connect and disconnect under pressure	■	■	■
Interchange with similar products		■	■
High impulse resistance	■	■	■
Up to 6000 psi rated pressure	■	■	■
Rotations to connect threaded sleeve	2-1/2	>6	>6
Damage resistant double start Acme thread	■		
Internal bearing prevents hose twist and eases connection	■		
Corrosion resistant zinc nickel plating	■		
Visual and tactile connection indicator	■	(Visual indicator only)	(Visual indicator only)
Stainless non-spill valve	■	■	
Local services and product support	■	■	

Contact Information:

Parker Hannifin Corporation
Quick Coupling Division
 8145 Lewis Road
 Minneapolis, MN 55427

phone 763 544 7781
 fax 763 544 3418
 qcd_sales@parker.com

www.parker.com/quickcouplings



ENGINEERING YOUR SUCCESS.