



▶▶ *Hydraulic*  
**Express Program**

**PV+ Piston Pump**

WI-MK173A



ENGINEERING YOUR SUCCESS.

## PV+ Piston Pump



### PV+ Piston Pumps have the following features.

- Open circuit axial piston pump
- 5000 psi continuous
- Maximum volume stop
- Rear drive kits can be added to all units
- 3D CAD models available on line

### Stocked Pumps have the following features.

- Keyed shaft
- Clockwise rotation
- Remote pressure compensator

### Together, we can deliver.

- Stocked Units have a List Price Reduction
- Available to all PCD Distributors at standard discounts
- Pumps are largest displacement in frame size but have special price that is same as smallest displacement in frame size

Part Number
PV028R1D3T1NMRC
PV046R1D3T1NMRC
PV092R1D3T1NMRC
PV180R1D3T1VMRC
PV270R1D3T1VMRC

© 2021 Parker Hannifin Corporation. All Rights Reserved.



#### Parker Canada Division

Milton (905) 693-3000  
Montreal (514) 684-3000  
Calgary (403) 291-9284

pcdmktg@parker.com

#### Parker Policy MI-WK173A

Confidential  
Effective Date: Nov 23, 2021  
Issue Date: Nov 23, 2021  
Supersedes: Nov 29, 2019  
[www.parker.com/canada](http://www.parker.com/canada)