

Quick Couplings Euro Profile - Air Applications

		Flow Functions				Nominal Diameter (mm)	Flow (l/min)	Series
Body Material	Seal Material	 Single Shut-Off KA	 Safety Straight through KR	 Safety Single Shut-Off KS	 Self Venting KE			
Standard Environment	Brass	•				2,7	165	Series 20
		•	•	•		5	550	Series 21
		•				7,4	1070	Series 26
	Nickel-Plated Brass *Steel	•				2,7	165	Series 20
		•	•	•		5	550	Series 21
					•	7,4	1070	Series 26
		•	•	•		7,8	1800	Series 25
		•			•	7,8	2020	Series 1600*
		•				10	2400	Series 27
		•			•	10	3500	Series 1700*
Harsh Environment	Stainless Steel	•				2,7	165	Series 20
		•				5	550	Series 21
		•				7,8	1800	Series 25
		•				10	2400	Series 27



Quick Couplings Euro Profile

Liquids & Gas Applications

	Body Material	Seal Material			Flow Functions				Nominal Diameter (mm)	Flow (l/min)	Series
		NBR	EPDM	FKM	 Straight Through KF	 Double Shut-Off KB	 Safety Double Shut-Off KD	 Dry Brake KL			
Standard Liquids & Gas Standard Environment	Nickel-Plated Brass	•	•	•	•	•			2,7	1,2	Series 20
		•	•	•	•	•	•	•	5	2,7	Series 21
		•	•	•	•	•	•	•	7,8	7,1	Series 25
		•	•	•	•	•		•	10	14	Series 27
Aggressive Liquids & Gas Harsh Environment	Stainless Steel		•	•		•			2,7	1,2	Series 20
			•	•		•		•	5	2,7	Series 21
			•	•		•		•	7,8	7,1	Series 25
			•	•		•		•	10	14	Series 27

