


Pressure Regulator

Functional Specifications:

Valve type	Regulator /Normally opened
Fluid media	Natural Gas, Air (Lubricate)
Mounting position	The preferred orientation is vertical and upright.
External Leakage	Less than 1cc/min. at 25Kgf/cm ²



Physical Specifications:

Body/Cover Material	Aluminum
Seal Material	NBR
Piston, Disc, Spring	Aluminum, PTFE, Stainless steel 304
Process Connection	1/2NPT or 3/4UNF
	BSP(g), NPT available

Operating Specifications

Fluid Temperature	NBR Seal:- 40 to 120°C
Maximum Operating Pressure	25Kgf/cm ²
Orifice	8.5mm
Proof Pressure	In Pressure:10~12Kgf/cm ² Out Pressure:7.3~7.5Kgf/cm ²
Proof Flow	166L/min(60Kg/h)

Applications:

Natural Gas Engine
Commercial Equipments

Dimensions

