

Air Driven, High Pressure Liquid Pumps

Condensed Product Catalog

Catalog: 02-9326BE

May 2015

aerospace climate control electromechanical filtration fluid & gas handling hydraulics pneumatics process control sealing & shielding





Table of Contents

Introduction	2
Pump Series Models	3
Drive Types	3
Quick Reference Guide	4
Pump Operation	5
Air Drive Section	5
Typical Pump Cut-away	6
Pump Special Features	
ACL Series Pump	8
ACHL Series Pump	10
ASL Series Pump	12
AHL Series Pump	18
AFL Series Pump	22
Packaged Pressure Systems	25

Introduction

Parker Autoclave Engineers has always been a large user of Air-over-Liquid pump technology and has a lifetime of experience using all variety of pumps in many different configurations. We have used this experience to develop a best-in-breed line of air-driven, high pressure pumps that are efficient to operate, simple in design, and will stand the test of time. Compared to other types of hydraulic pumps, they provide cost effective and energy saving benefits for many applications in the Oil and Gas, Chemical, Industrial and Research industries.

These pumps convert simple air pressure into high and ultra-high liquid pressures by utilizing a large area piston on the air side to move a small area plunger to compress the liquid into very high hydraulic pressures - as high as 60,000 psi (4137 bar). Some designs are for economy, some for manual use, some for low-flow & high pressure, some for high flow & medium pressure... Choice – what a concept! Pumps like these are perfect for product testing, valve actuation, chemical injection and other applications that require intense pressure. When used in conjunction with a Hydraulic Intensifier (another PAE product) pressures to 150,000 psi (10,000 bar) are normal.

Parker Autoclave Engineers has been making pressure and corrosion test systems as well as high pressure laboratory reaction vessels for over 70 years. Packaged Pressure Systems incorporating these Air-Driven, High Pressure Liquid pumps, plus our valves, fittings and other instrumentation was an automatic success story. We have created a wide range of self-contained portable, custom framed modules that "plug and play" for virtually any pressure test, control, or injection system you can imagine. They vary in size, flow capability, output pressure and can include optional features such as chart recording, data logging, cycle counters, injection controllers and almost any kind of electric or pneumatic valve control option.







Pump Series Models



ASL Series:

- Standard Liquid Pump
- Pressures up to 60,000 psi (4137 bar)
- Approximately 6 inches in diameter air piston
- Broad range of ratios



ACL Series:

- Compact Liquid Pump
- Pressures up to 31,900 psi (2199 bar)
- Approximately 3 inches in diameter air piston



ACHL Series:

- ACL Series Pump with hand lever
- Pressures up to 31,900 psi (2199 bar)
- Precise Pressure control operation, pump is spring returned



AHL Series:

- High Flow Liquid
- Pressures up to 13,300 psi (917 bar)
- Approximately 10 inches in diameter air piston
- Dual Acting



AFL Series:

- High Flow, High Pressure
- Pressures up to 12,500 psi (862 bar)
- Flow up to 3 gpm
- Dual Acting

Drive Types



Catalog Number Example: ACL189-01

Quick Reference Guide

Dumn Model	Pressure	Maximum Rated	Displacement	Liquid Connections			
Pump Model Series	Series Ratio		Per Cycle .in³ (cm³)	Inlet	Outlet		
ACL Series							
ACL72-01	1:88	12,500 (862)	0.09 (1.47)	3/8" FNPT	F250C		
ACL111-01	1:130	18,850 (1,300)	0.05 (0.8)	3/8" FNPT	F250C		
ACL189-01	1:220	31,900 (2,199)	0.04 (0.7)	3/8" FNPT	F250C		
ACL189-02	1:440	60,000 (4,137)	0.04 (0.7)	3/8" FNPT	F250C		
ACIII Corico							
ACHL Series ACHL72-01	1:84	12 500 (962)	0.00 (1.47)	3/8" FNPT	F250C		
		12,500 (862)	0.09 (1.47)				
ACHL189-01	1:213	31,900 (2,1990)	0.035 (0.57)	3/8" FNPT	F250C		
ASL Series							
ASL10-01	1:11	1,600 (110)	5.22 (85.5)	1" FNPT	1/2" FNPT		
ASL15-01	1:16	2,300 (159)	3.62 (59.3)	1" FNPT	1/2" FNPT		
ASL25-01	1:28	4,000 (276)	2.10 (34.4)	1/2" FNPT	1/2" FNPT		
ASL35-01	1:39	5,600 (386)	1.50 (24.64)	1/2" FNPT	1/2" FNPT		
ASL60-01	1:70	10,000 (689)	0.84 (13.8)	1/2" FNPT	1/2" FNPT		
ASL100-01	1:113	15,000 (1,034)	0.52 (8.5)	1/2" FNPT	1/2" FNPT		
ASL150-01	1:150	21,500 (1,482)	0.39 (6.4)	1/2" FNPT	F250C		
ASL250-01	1:265	38,400 (2,648)	0.22 (3.6)	1/2" FNPT	F250C		
ASL400-01	1:398	57,700 (3,978)	0.14 (2.3)	1/2" FNPT	F250C		
ASL10-02	1:22	3,200 (221)	5.22 (85.5)	1" FNPT	1/2" FNPT		
ASL15-02	1:32	4,600 (317)	3.62 (59.3)	1" FNPT	1/2" FNPT		
ASL25-02	1:56	8,100 (558)	2.10 (34.4)	1/2" FNPT	1/2" FNPT		
ASL35-02	1:78	11,200 (772)	1.50 (24.64)	1/2" FNPT	1/2" FNPT		
ASL60-02	1:140	20,000 (1,379)	0.84 (13.8)	1/2" FNPT	9/16" SF562C		
ASL100-02	1:226	31,000 (2,137)	0.52 (8.5)	1/2" FNPT	F250C		
ASL150-02	1:300	43,000 (2,965)	0.39 (6.4)	1/2" FNPT	F250C		
ASL250-02	1:530	60,000 (4,137)	0.22 (3.6)	1/2" FNPT	F250C		
ASL400-02	1:796	60,000 (4,137)	0.14 (2.3)	1/2" FNPT	F250C		
AHL Series							
AHL33-2D	1:67	6,700 (462)	15.3 (250.7)	1" FNPT	1/2" FNPT		
AHL66-2D	1:133	13,300 (917)	7.8 (127.8)	1/2" FNPT	1/2 TNI T		
		, - (- /	` -1				
AFL Series							
AFL35-1D	1:39	5,600 (386)	6.02 (98.7)	1" FNPT	9/16" SF562C		
AFL60-1D	1:70	10,000 (690)	3.40 (55.7)	1" FNPT	9/16" SF562C		
AFL100-1D	1:113	15,000 (1034)	9/16" SF562C				

Pump Operation

Piston to Plunger Ratio


- Compressed air is used to produce hydraulic pressure
- Works on differential surface area between the large air piston and smaller hydraulic plunger
- Differential is represented by the pressure ratio of the pump

Pressure Ratio = Area of Air Piston ÷ Area of Hydraulic Plunger

• The higher the pressure ratio, the higher the output hydraulic pressure

Pressure Output = Pressure Ratio x Air Drive Pressure

- When air is applied to the pump it will cycle until the forces on the air piston equals the forces on the hydraulic plunger. This is the stall pressure.
- Pump will automatically restart if there is a drop in hydraulic pressure or an increase in air drive pressure.
- Double air pistons available which will double the pressure ratio because you have twice the air piston area acting on the same hydraulic plunger area.




Air Drive Section

- Compressed air is used to produce hydraulic pressure
- · Works on differential surface area between the large air piston and smaller hydraulic plunger
- Differential is represented by the pressure ratio of the pump


Section 1

- Air pilot operated spool provides automatic cycling of air from one side of the piston to the other
- At the end of each stroke, the air piston activates a pilot valve that will cause the spool to shift




Section 2

- The spool shifting will supply air to one side of the piston while venting the other side of the piston
- This alternating action continues until the pump reaches its stall pressure



Typical Pump Cut-Away



	Description		Description
Α	Air Inlet	I	Air Piston Bumper
В	Top End Cap	J	Air Piston
С	Air Muffler	К	High Pressure Seal Assembly
D	Air Cylinder	L	Liquid Inlet Connection
Е	Bottom End Cap	M	Inlet Check Valve
F	High Pressure Outlet Connection	N	Pump Head Body
G	Outlet Check Valve	0	Hydraulic Plunger
Н	Pilot Valve		

Pump Special Features & Benefits

- All Aluminum parts machined from high quality bar stock, not cast aluminum components
- Anodizing with special sealing technique to provide better protection from harsh environments
- Muffler specified to give a great combination of high flow and low noise
- Rubber bumpers in end caps to reduce noise of operation
- Latest lubrication technology provides long seal service life and improves pump efficiency and performance
- No lubricator required for air drive source
- Stainless steel tie-rods and hardware
- Stainless plunger coated with a proprietary multi-layer carbon based coating with diamond like carbon exterior layer:
 - High hardness (3 times harder than Stellite)
 - Inert, it has superior chemical compatibility and corrosion resistance
 - Low friction that limits seal wear and increases efficiency (coefficient of friction equal to or less than PTFE)
 - Tough coating that provides long plunger cycle life. (Have never had to replace a coated plunger during prototype testing)
- · Pressure head specially designed and engineered for high cycle life
- Spring energized u-cup seal provides better sealing performance at wide ranges of pressures
- Extended service life check valves with Ceramic balls for high pressure applications

ACL SERIES Single-Acting, Single Piston Air Drive

• Single-Acting, Single or Double Piston Air Drive

 Service: Oil, Water, Water/Oil mixture and other fluids depending on material compatibility

• Maximum Operating Temperature: 0-140° F (-18° to 60° C)

• Net Weight: 8 lbs. (3.6 kg)

• Pressure Head: 316 Stainless Steel

• Plunger: 440 Stainless Steel

Check Valve Glands: 15-5PH Stainless SteelLiquid Seal: see Ordering Guide for options


· Air Drive Seals: Buna N





Reference Guide


Dump Madal	Duman Madel Dressure	Maximum Rated	Displacement	Liquid Connections			
Pump Model Series	Pressure Ratio	Outlet Pressure PSI (bar)	Per Cycle .in³ (cm³)	Inlet	Outlet		
ACL Series							
ACL72-01	1:88	12,500 (862)	0.09 (1.47)	3/8" FNPT	F250C		
ACL111-01	1:130	18,850 (1,300)	0.05 (0.08)	3/8" FNPT	F250C		
ACL189-01	1:220	31,900 (2,199)	0.04 (0.07)	3/8" FNPT	F250C		
ACL189-02	1:440	60,000 (4,137)	0.04 (0.07)	3/8" FNPT	F250C		

Air Drive Connection - All ACL series pumps have a 1/4" FNPT main air drive supply connection









Each mounting bracket includes (2) x 3/8" (9.53) slots for 5/16" bolts.

Bottom inlet pump head and side inlet pump head are mutually exclusive.

All dimensions are for reference only and are subject to change without notice.

Primary dimensions: Inches Secondary Dimensions: (Millimeters)

Ordering Guide

Typical catalog number example: ACL189-01SNP (catalog number is created based on customer selection of product parameters, see below for example)								
ACL189-01 S N P								
Pump Series Type/Size/Ratio	Liquid Inlet Location	Isolation Chamber	Liquid Seal Material					
• Compact Liquid High Pressure Pump • 3" Single Piston Air Drive • 1:220 Air-to-Liquid Pressure Ratio • Maximum 31,900 psi (2,199 bar)	S* = Side B = Bottom	N* = None	P* = UHMWPE U-Cup with Elgiloy Spring Energizer U = Urethane U-Cup					

^{*} Standard for stock pumps

Flow Rate Table: Air Drive Pressure (psi) vs. Outlet Pressure (psi)

Catalog	Air Drive					0	utlet Pre	ssure (p	si)				
Number	Pressure (psi)	0	500	1,500	3,000	5,000	7,500	10,000	15,000	25,000	40,000	55,000	
	60	42	32	17	9	1							
ACL72-01	90	42	34	25	18	7	1						
	120	43	35	29	24	17	7	2					
	60	28	23	14	9	5	1						
ACL111-01	90	28	25	19	15	10	5	2					
	120	29	26	21	18	15	10	6	1				in ³ /min.
	60	15	15	14	13	12	9	6					
ACL189-01	90	15	15	15	14	14	13	11	6				
	120	15	15	15	15	15	14	13	10	1			
	60	13	12	11	10	9	7	7	5	1			
ACL189-02	90	14	13	12	11	8	8	8	7	5			
	120	17	16	14	12	10	9	8	8	7	4		

ACHL SERIES Single-Acting, Single Air Drive with Hand Lever


- Single-Acting, Single Air Drive with Hand Lever
- Service: Oil, Water, Water/Oil mixture and other fluids depending on material compatibility
- Standard Hand Lever for precise pressure control, remote locations or emergency back-up applications.
- Maximum Operating Temperature: 0-140° F (-18° to 60° C)
- Net Weight: 8 lbs. (3.6 kg)
- Pressure Head: 316 Stainless Steel
- Plunger: 440 Stainless Steel
- Check Valve Glands: 15-5PH Stainless Steel
- · Liquid Seal: see Ordering Guide for options
- Air Drive Seals: Buna N





Reference Guide


Dumm Madal	Dusassura	Maximum Rated	Displacement	Liquid Connections			
Pump Model Series	Pressure Ratio	Outlet Pressure PSI (bar)	Per Cycle .in³ (cm³)	Inlet	Outlet		
ACHL Series							
ACHL72-01	1:84	12,500 (862)	0.09 (1.47)	3/8" FNPT	F250C		
ACHL189-01	1:213	31,900 (2,199)	0.035 (0.57)	3/8" FNPT	F250C		

Air Drive Connection - All ACHL series pumps have a 1/4" FNPT main air drive supply connection









Note:

Each mounting bracket includes (2) x 11/32" (8.73) slots for 5/16" bolts. Bottom inlet pump head and side inlet pump head are mutually exclusive. All dimensions are for reference only and are subject to change without notice.

Primary dimensions: Inches

Secondary Dimensions: (Millimeters)

Ordering Guide

Typical catalog number example: ACHL189-01SNP (catalog number is created based on customer selection of product parameters, see below for example)							
ACHL189-01 S N P							
Pump Series Type/Size/Ratio	Liquid Inlet Location	Isolation Chamber	Liquid Seal Material				
ACHL Compact Liquid High Pressure Pump with hand lever 3" Single Piston Air Drive 1:213 Max. Air-to-Liquid Pressure Ratio Maximum 31,900 psi (2,199 bar)	S* = Side B = Bottom	N* = None	P* = UHMWPE U-Cup with Elgiloy Spring Energizer U = Urethane U-Cup				

^{*} Standard for stock pumps

Flow Rate Table: Air Drive Pressure (psi) vs. Outlet Pressure (psi)

Catalog	Air Drive	Air Drive Outlet Pr				utlet Pre	ssure (p	si)					
Number	Pressure (psi)	0	500	1,500	3,000	5,000	7,500	10,000	15,000	25,000	40,000	55,000	
	60	42	32	17	9	1							
ACHL72-01	90	42	34	25	18	7	1						
	120	43	35	29	24	17	7	2					in ³ /min.
	60	15	15	15	15	14	13	8					
ACHL189-01	90	15	15	15	15	15	13	11	7				
	120	15	15	15	15	15	13	12	8	1			

ASL SERIES Single-Acting, Single or Double Piston Air Drive

• Single-Acting, Single and Double Piston Air Drive

• Service: Oil, Water, Water/Oil mixture and other fluids depending on material compatibility

• Maximum Operating Temperature: 0-140° F (-18° to 60° C)

• Pressure Head: 316 Stainless Steel

• Check Valve Glands: 316 Stainless Steel

• Liquid Seal: see Ordering Guide for options

· Air Drive Seals: Buna N



Reference Guide

Dump Madal	Pump Model Pressure		Displacement	Liquid Connections			
Series	Ratio	Outlet Pressure PSI (bar)	Per Cycle .in³ (cm³)	Inlet	Outlet		
ASL Series							
ASL10-01	1:11	1,600 (110)	5.22 (85.5)	1" FNPT	1/2" FNPT		
ASL15-01	1:16	2,300 (159)	3.62 (59.3)	1" FNPT	1/2" FNPT		
ASL25-01	1:28	4,000 (276)	2.10 (34.4)	1/2" FNPT	1/2" FNPT		
ASL35-01	1:39	5,600 (386)	1.50 (24.64)	1/2" FNPT	1/2" FNPT		
ASL60-01	1:70	10,000 (689)	0.84 (13.8)	1/2" FNPT	1/2" FNPT		
ASL100-01	1:113	15,000 (1,034)	0.52 (8.5)	1/2" FNPT	1/2" FNPT		
ASL150-01	1:150	21,500 (1,482)	0.39 (6.4)	1/2" FNPT	F250C		
ASL250-01	1:265	38,400 (2,648)	0.22 (3.6)	1/2" FNPT	F250C		
ASL400-01	1:398	57,700 (3,978)	0.14 (2.3)	1/2" FNPT	F250C		
ASL10-02	1:22	3,200 (221)	5.22 (85.5)	1" FNPT	1/2" FNPT		
ASL15-02	1:32	4,600 (317)	3.62 (59.3)	1" FNPT	1/2" FNPT		
ASL25-02	1:56	8,100 (558)	2.10 (34.4)	1/2" FNPT	1/2" FNPT		
ASL35-02	1:78	11,200 (772)	1.50 (24.64)	1/2" FNPT	1/2" FNPT		
ASL60-02	1:140	20,000 (1,379)	0.84 (13.8)	1/2" FNPT	9/16" SF562CX		
ASL100-02	1:226	31,000 (2,137)	0.52 (8.5)	1/2" FNPT	F250C		
ASL150-02	1:300	43,000 (2,965)	0.39 (6.4)	1/2" FNPT	F250C		
ASL250-02	1:530	60,000 (4,137)	0.22 (3.6)	1/2" FNPT	F250C		
ASL400-02	1:796	60,000 (4,137	0.14 (2.3)	1/2" FNPT	F250C		

Ordering Guide

Typical catalog number example: ASL250-01SNP (catalog number is created based on customer selection of product parameters, see below for example)							
ASL250-01 S N P							
Pump Series Type/Size/Ratio	Liquid Inlet Location	Isolation Chamber	Liquid Seal Material				
ASL	S* = Side	N* = None	P* = UHMWPE U-Cup				
Standard Liquid High Pressure Pump	B = Bottom	C = Included	(See table below)				
6" Single Piston Air Drive							
• 1:265 Max. Air-to-Liquid Pressure Ratio							
 Maximum 38.400 psi (2.648 bar) 							


^{*} Standard for stock pumps


Available seal material for the following models.

Seal Material
*PV = UHMWPE U-Cup and Viton O-Rings
PE = UHMWPE U-Cup and EPDM O-Rings
PB = UHMWPE U-Cup and Buna-N O-Rings
PC = UHMWPE U-Cup and Perfluoroelastomer O-Rings
UV = Urethane U-Cup and Viton O-Rings
UE = Urethane U-Cup and EPDM O-Rings
UB = Urethane U-Cup and Buna-N O-Rings
TV = Thermoplastic Polyester U-Cup and Viton O-Rings
TE = Thermoplastic Polyester U-Cup and EPDM 0-Rings
TB = Thermoplastic Polyester U-Cup and Buna-N O-Rings
TC = Thermoplastic Polyester U-Cup and Perfluoroelastomer O-Rings
*PV = UHMWPE U-Cup and Viton O-Rings
PE = UHMWPE U-Cup and EPDM O-Rings
PB = UHMWPE U-Cup and Buna-N O-Rings
PC = UHMWPE U-Cup and Perfluoroelastomer O-Rings
UV = Urethane U-Cup and Viton O-Rings
UE = Urethane U-Cup and EPDM 0-Rings
UB = Urethane U-Cup and Buna-N O-Rings
*P = UHMWPE U-Cup with Elgiloy Spring 0-Rings
UV = Urethane U-Cup and Viton O-Rings
UE = Urethane U-Cup and EPDM 0-Rings
UB = Urethane U-Cup and Buna-N O-Rings
*P = UHMWPE U-Cup
UE = Urethane U-Cup

^{*} Standard for stock pumps

<u>Air Drive Connection</u> - All ASL series pumps have a 1/2" FNPT main air drive supply connection and utilize a 1/8" FNPT pilot port connection for remote start/stop operation. It is recommended to operate the pilot port at a higher air pressure than the main air drive supply pressure for proper function.








Each mounting bracket includes (2) \times 11/32" (8.73) slots for 5/16" bolts. Bottom inlet pump head and side inlet pump head are mutually exclusive. All dimensions are for reference only and are subject to change without notice.

Primary dimensions: Inches Secondary Dimensions: (Millimeters)



ASL Series: Dimensions

Pump Model Series	As	B _S	Cs	D _S	E _S	F _S	G _S
Single Piston Air	Drive						
ASL10-01	6.87 (175)	8.25 (210)	9.83 (250)	12.51 (318)	3.27 (83)	7.57 (192)	3.95 (100)
ASL15-01	6.87 (175)	8.25 (210)	9.83 (250)	12.51 (318)	3.27 (83)	7.57 (192)	3.95 (100)
ASL25-01	6.87 (175)	8.25 (210)	9.83 (250)	11.54 (293)	3.27 (83)	6.92 (176)	3.95 (100)
ASL35-01	6.87 (175)	8.25 (210)	9.83 (250)	11.54 (293)	3.27 (83)	6.92 (176)	3.95 (100)
ASL60-01	6.87 (175)	8.31 (211)	9.25 (235)	12.10 (307)	3.43 (87)	7.24 (184)	3.95 (100)
ASL100-01	6.87 (175)	8.31 (211)	9.25 (235)	12.10 (307)	3.43 (87)	7.24 (184)	3.95 (100)
ASL150-01	6.87 (175)	8.31 (211)	9.25 (235)	11.55 (293)	4.18 (106)	7.45 (189)	3.95 (100)
ASL250-01	6.87 (175)	8.31 (211)	9.25 (235)	11.55 (293)	4.18 (106)	7.45 (189)	3.95 (100)
ASL400-01	6.87 (175)	8.37 (213)	9.39 (239)	11.74 (298)	2.75 (70)	6.13 (156)	3.95 (100)
Pump Model Series	AD	BD	CD	DD	ED	FD	GD
Double Piston Air	Drive						
ASL10-02	10.81 (275)	12.19 (310)	13.77 (350)	16.45 (418)	3.27 (83)	7.57 (192)	3.95 (100)
ASL15-02	10.81 (275)	12.19 (310)	13.77 (350)	16.45 (418)	3.27 (83)	7.57 (192)	3.95 (100)
ASL25-02	10.81 (275)	12.19 (310)	13.77 (350)	15.48 (393)	3.27 (83)	6.92 (176)	3.95 (100)
ASL35-02	10.81 (275)	12.19 (310)	13.77 (350)	15.48 (393)	3.27 (83)	6.92 (176)	3.95 (100)
ASL60-02	10.81 (275)	12.25 (311)	13.19 (335)	16.04 (407)	3.43 (87)	7.24 (184)	3.95 (100)
ASL100-02	10.81 (275)	12.25 (311)	13.19 (335)	15.50 (394)	4.18 (106)	7.24 (184)	3.95 (100)
ASL150-02	10.81 (275)	12.25 (311)	13.19 (335)	15.50 (394)	4.18 (106)	7.45 (189)	3.95 (100)
			i				
ASL250-02	10.81 (275)	12.30 (312)	13.32 (338)	15.68 (398)	2.75 (70)	7.45 (189)	3.95 (100)

Note

Each mounting bracket includes two (2) \times 13/32" (10.32) slots for 3/8" bolts. Bottom inlet pump head and side inlet pump head are mutually exclusive. All dimensions are for reference only and are subject to change without notice.

Primary Dimensions: Inches Secondary Dimensions: (Millimeters)

Flow Rate Table: Air Drive Pressure (psi) vs. Outlet Pressure (psi)

Catalog	Air Drive	Outlet Pressure (psi)											
Number	Pressure (psi)	0	500	1,500	3,000	5,000	7,500	10,000	15,000	25,000	40,000	55,000	
	60	1277	489										
ASL10-01	90	305	826										
	120	1360	925										
	60	887	485										
ASL15-01	90	906	591										
	120	945	642	474									
	60	508	342	127									
ASL25-01	90	520	387	303									
	120	543	427	360	202								
	60	315	273	121									
ASL35-01 ASL60-01	90	322	291	211	58								
	120	328	302	250	157								
	60	168	155	125	79								
	90	175	161	134	106	63							
	120	182	167	140	118	94	45						
	60	104	99	88	70	46							
ASL100-01	90	108	103	92	78	65	44	11					
	120	112	106	95	83	72	60	47					
	60	81	79	76	66	49	19						in ³ /min.
ASL150-01	90	83	82	80	75	67	53	35					
	120	84	83	82	78	73	66	55	25				
	60	46	45	44	42	37	26	20	2				
ASL250-01	90	47	46	45	44	43	40	36	26				
	120	48	47	47	46	45	43	41	34	17			
	60	39	38	37	36	33	29	23	10				
ASL400-01	90	40	39	38	38	37	35	32	26	8			
	120	41	40	39	38	38	37	36	32	21			
	60	880	720										
ASL10-02	90	890	800	350									
	120	900	840	570									
	60	615	550	200									
ASL15-02	90	625	575	410									
	120	630	600	500	225								
	60	345	330	265	60								
ASL25-02	90	350	335	300	208	15							
	120	355	345	320	265	150							
	60	240	230	210	115								
ASL35-02	90	242	232	225	190	115							
	120	245	235	230	210	170	95						

Catalog	Air Drive					Outlet	Pressur	e (psi)					
Number	Pressure (psi)	0	500	1,500	3,000	5,000	7,500	10,000	15,000	25,000	40,000	55,000	
	60	150	148	145	120	70	2						
ASL60-02	90	155	152	147	136	117	80	33					
	120	157	154	152	145	133	112	82	8				
	60	86	84	82	77	72	53	30					
ASL100-02	90	87	86	84	82	82	70	61	36				
	120	89	88	86	84	84	77	72	57	13			
	60	64	64	63	60	57	50	38	14				in ³ /min.
ASL150-02	90	65	65	64	62	60	57	53	41	9			
	120	66	66	65	64	63	61	58	51	32			
	60	37	36	36	35	35	34	32	27	12			
ASL250-02	90	37	36	36	36	36	36	34	31	25	10		
	120	37	37	36	36	36	36	35	34	30	21	9	
	60	31	31	30	30	29	29	28	26	16			
ASL400-02	90	31	31	31	30	30	30	29	27	23	14	2	
	120	31	31	31	31	30	30	30	29	27	21	14	

AHL SERIES Double-Acting, Double Piston Air Drive

• Service: Oil, Water, Water/Oil mixture and other fluids depending on material compatibility

• Maximum Operating Temperature: 0-140° F (-18° to 60° C)

• Pressure Head: 15-5 PH Stainless Steel

• Check Valve Glands: 316 Stainless Steel

• Liquid Seal: see Ordering Guide for options


· Air Drive Seals: Buna N




Reference Guide

Duman Madal	Dueseume	Maximum Rated	Displacement	Liquid Connections		
Series	Pump Model Pressure Series Ratio		Per Cycle .in³ (cm³)	Inlet	Outlet	
AHL Series						
AHL33-2D	1:67	6,700 (462)	15.3 (250.7)	1" FNPT	1/2" FNPT	
AHL66-2D	1:133	13,300 (917)	7.8 (127.8)	1/2" FNPT	1/2" FNPT	

Air Drive Connection - All AHL series pumps have a 1" FNPT main air drive supply connection and utilize a 1/8" FNPT pilot port connection for remote start/stop operation. It is recommended to operate the pilot port at a higher air pressure than the main air drive supply pressure for proper function.



Side View



Front View

Note:

Each mounting bracket includes (2) x 9/16" (8.73) slots for 1/2" bolts. Bottom inlet pump head and side inlet pump head are mutually exclusive. All dimensions are for reference only and are subject to change without notice. Primary dimensions: Inches

Primary dimensions: Inches Secondary Dimensions: (Millimeters)

Model	А	В
AHL66	32.66 (829.61)	30.16 (766.11)
AHL33	32.41 (823.21)	30.42 (772.41)

Ordering Guide

Typical catalog number example: **AHL66-2DSCUV** (catalog number is created based on customer selection of product parameters, see below for example)

AHL66-2D	S	С	UV
Pump Series Type/Size/Ratio	Liquid Inlet Location	Isolation Chamber	Liquid Seal Material (AHL33 and AHL66)
AHL High Flow Liquid High Pressure Pump 10" Dual Piston Air Drive 1:133 Max. Air-to-Liquid Pressure Ratio Maximum 13,300 psi (917 bar) Double Acting Liquid Heads	S* = Side	C* = Included	UV* = Urethane U-Cup and Viton O-Rings UE = Urethane U-Cup and EPDM O-Rings UB = Urethane U-Cup and Buna-N O-Rings TV = Thermoplastic Polyester U-Cup and Viton O-Rings TE = Thermoplastic Polyester U-Cup and EPDM O-Rings TB = Thermoplastic Polyester U-Cup and Buna-N O-Rings TC = Thermoplastic Polyester U-Cup and Perfluoroelastomer O-Rings

^{*} Standard for stock pumps

Liquid Flow Rate vs. Outlet Pressure:

AHL33-2DSC Series

Approximate Air Drive Pressure: 100 psi									
Pressure (PSI)	Pressure (bar)	Flow (gpm)	Flow (liter/min)						
0	0	7.6* (see note 2)	28.8* (see note 2)						
1000	69	6.1	23.0						
2000	138	5.7	21.5						
3000	207	4.9	18.4						
4000	276	4.0	15.2						
5000	345	3.2	12.3						
6000	414	1.8	6.9						

Nominal Liquid Pressure (Stalled)									
Air Drive	Pressure	Liquid Pressure							
PSI	bar	PSI	bar						
20	1.4	1340	92.4						
30	2.1	2010	138.6						
40	2.8	2680	184.8						
50	3.4	3350	231.0						
60	4.1	4020	277.2						
70	4.8	4690	323.4						
80	5.5	5360	369.6						
90	6.2	6030	415.8						
100	6.9	6700	461.9						

Liquid Flow Rate vs. Outlet Pressure:

AHL66-2DSC Series

	Approximate Air Driv	ve Pressure: 100 psi		
Pressure (PSI)	Pressure (bar)	Flow (gpm)	Flow (liter/min)	
0	0	3.6* (see note 2)	13.7* (see note 2)	
1000	69	3.4	12.9	
2000	138	3.1	12.0	
3000	207	2.9	11.2	
4000	276	2.7	10.3	
5000	345	2.5	9.5	
6000	414	2.3	8.7	
7000	483	2.2	8.2	
8000	552	2.0	7.7	
9000	621	1.8	6.7	
10000	690	1.5	5.7	
11000	759	1.3	4.8	
12000	828	1.0	3.9	

Nominal Liquid Pressure (Stalled)								
Air Drive	Pressure	Liquid Pressure						
PSI	bar	PSI	bar					
20	1.4	2660	183.4					
30	2.1	3990	275.2					
40	2.8	5320	366.9					
50	3.4	6650	458.6					
60	4.1	7980	550.3					
70	4.8	9310	642.1					
80	5.5	10640	733.8					
90	6.2	11970	825.5					
100	6.9	13300	917.2					

Note:
1. Actual flow rates will vary depending on air flow capacity, downstream flow restrictions, and fluid type.
2. Flow valve at approximately 50 psi air drive pressure.

AFL SERIES Double-Acting, Single Piston Air Drive

 Service: Oil, Water, Water/Oil mixture and other fluids depending on material compatibility

• Maximum Operating Temperature: 0-140° F (-18° to 60° C)

Pressure Head: 15-5 PH Stainless SteelCheck Valve Glands: 316 Stainless Steel

• Liquid Seal: see Ordering Guide for options


· Air Drive Seals: Buna N




Reference Guide

Duran Madal	Dunganung	Maximum Rated	Displacement	Liquid Connections				
Pump Model Series	Pressure Ratio	Outlet Pressure PSI (bar)	Per Cycle in ³ (cm ³)	Inlet	Outlet			
AFL Series	AFL Series							
AFL35-1D	1:39	5,600 (386)	6.02 (98.7)	1" FNPT	9/16" SF562CX			
AFL60-1D	1:70	10,000 (690)	3.40 (55.7)	1" FNPT	9/16" SF562CX			
AFL100-1D	1:113	15,000 (1034)	2.30 (37.7)	1" FNPT	9/16" SF562CX			

<u>Air Drive Connection</u> - All ASL series pumps have a 1" FNPT main air drive supply connection and utilize a 1/8" FNPT pilot port connection for remote start/stop operation. It is recommended to operate the pilot port at a higher air pressure than the main air drive supply pressure for proper function.



Bottom View



Right View Front View

Note:

Each mounting bracket includes (2) x 9/16" (14.29) slots for 1/2" bolts. Bottom inlet pump head and side inlet pump head are mutually exclusive. All dimensions are for reference only and are subject to change without notice. Primary dimensions: Inches Secondary Dimensions: (Millimeters)

Ordering Guide

Typical catalog number example: AFL100-1DBPV (catalog number is created based on customer selection of product parameters, see below for example) C **AFL100-1D** В PV **Pump Series Liquid Inlet** Isolation **Liquid Seal Material** (AFL35, AFL60, AFL100) Type/Size/Ratio Location Chamber $\mathbf{C}^{\star} = \text{Included}$ **AFL** B* = Bottom**PV*** = UHMWPE U-Cup and Viton O-Rings • High Flow, High Pressure Pump **PE** = UHMWPE U-Cup and EPDM O-Rings • 6" Dual Piston Air Drive **PB** = UHMWPE U-Cup and Buna-N O-Rings • 1:113 Max. Air-to-Liquid Pressure Ratio **PC** = UHMWPE U-Cup and Perfluoroelastomer O-Rings • Maximum 15,000 psi (1034 bar) • Single Ended, Double Acting Liquid Heads

Flow Rate Table: Air Drive Pressure (psi) vs. Outlet Pressure (psi)

Catalog	Air Drive		Outlet Pressure (psi)							
Number Pressure (psi)	0	500	1,500	3,000	4,500	6,000	10,000	15,000		
	60	24	19	9						
AFL35	90	25	21	16	6					
	120	26	23	19	12	2				Liters /min.
	60	14	12	9	4					
AFL60	90	14	13	11	8	6	1			
	120	15	14	12	10	8	6			
	60	10	9	7	5	3	1			
AFL100	90	11	10	8	7	6	5	1		
	120	12	11	9	8	7	6	3		

^{*} Standard for stock pumps

Packaged Pressure Systems

Since our beginning in 1946, Parker Autoclave Engineers has been the world's market leader in the development and manufacture of high and ultra-high pressure components, valves and systems. At our modern factory in Erie Pennsylvania, USA we have engineers with the specialized experience to design and create products commonly used to control pressures exceeding 100,000 psi (6900 bar) while consistently exceeding customer expectations.

Using the knowledge developed over the last 70 years, Parker Autoclave Engineers Packaged Pressure Systems have been developed to incorporate any of our Air-Driven, High Pressure Liquid pumps, valves and fittings into a wide range of self-contained portable, or custom framed modules that "plug and play" for virtually any test, control, or injection system you can imagine. They vary in size, flow capability, output pressure and can include optional features such as chart recording, data logging, cycle counters, injection controllers and almost any kind of electric or pneumatic valve control option. Applications include: Hydrostatic/Burst/Leak/Functional testing, Chemical injection, Valve/Hose/Gauge testing, Bolt tensioning, Hydraulic Control systems, Laboratory Research and Autofrettage systems.

Portable Pressure Systems

Move your high pressure test stand anywhere you need it to be...

Powder Coated Steel, Stainless Steel or Aluminum Frame Options
Single or Dual Pump Systems with or without reservoir
Utilizes any Combination ASL, ACL, ACHL, AFL, or AHL Air-Driven Liquid Pumps
Outlet Pressures to 60,000 PSI (4140 bar) — Flows to 7.6 GPM (29 lpm)
Vertical or Horizontal Frame Designs with Optional Casters
Totally Self Contained-Electricity not Required, Only Air
All Air Controls Included, No Lubrication Needed
Isolation Valves, Relief Valves, Rupture Disks, Stroke Counters
and other Options Available



Custom Pressure Systems

Modify the Standard Design to Incorporate Specified Instruments or Request Fit-for-Purpose Designs

Powder Coated Steel, Aluminum or Stainless Steel Open/Enclosed Frame Options Fit-for-Purpose Enclosures/Benches/Reels or Test Chambers
Utilize any Parker Autoclave Engineers Air-Driven Liquid Pump
Options Include All Standard Options plus: Remote Controlled Valves,
Chart Recorders, Data Loggers, PLC or Computer Controls, and Digital Displays.



Call for more information or visit us online at www.autoclave.com

Parker Worldwide

AE - UAE, Dubai Tel: +971 4 8875600 parker.me@parker.com

AR – Argentina, Buenos Aires Tel: +54 3327 44 4129 falecom@parker.com

AT – Austria, Wiener Neustadt Tel: +43 (0)2622 23501-0 parker.austria@parker.com

AT – Eastern Europe, Wiener Neustadt Tel: +43 (0)2622 23501 970 parker.easteurope@parker.com

AU – Australia, Dandenong Tel: +61 (0)3 9768 5555 customer.service.au@parker.com

AZ – Azerbaijan, Baku Tel: +994 50 2233 458 parker.azerbaijan@parker.com

BE/LX - Belgium, Nivelles Tel: +32 (0)67 280 900 parker.belgium@parker.com

BR - Brazil, Sao Jose dos Campos Tel: +55 12 4009 3504 falecom@parker.com

BY – Belarus, Minsk Tel: +375 17 209 9399 parker.belarus@parker.com

CA – Canada, Grimsby, Ontario Tel +1 905-945-2274 ipd_canada@parker.com

CH – Switzerland, Etoy Tel: +41 (0) 21 821 02 30 parker.switzerland@parker.com CL - Chile, Santiago Tel: +56 (0) 2 2303 9640 falecom@parker.com

CN - China, Shanghai Tel: +86 21 2899 5000 INGtechnical.china@parker.com

CZ - Czech Republic, Klecany Tel: +420 284 083 111 parker.czechrepublic@parker.com

DE – Germany, Kaarst Tel: +49 (0)2131 4016 0 parker.germany@parker.com

DK – Denmark, Ballerup Tel: +45 43 56 04 00 parker.denmark@parker.com

ES - Spain, Madrid Tel: +34 902 33 00 01 parker.spain@parker.com

FI - Finland, Vantaa Tel: +358 (0)20 753 2500 parker.finland@parker.com

FR - France, Contamine s/Arve Tel: +33 (0)4 50 25 80 25 parker.france@parker.com

GR – Greece, Athens Tel: +30 210 933 6450 parker.greece@parker.com

HU – Hungary, Budapest Tel: +36 1 220 4155 parker.hungary@parker.com

ID – Indonesia, Tangerang Tel: +62 (0)21 7588 1906 parker.id@parker.com IE - Ireland, Dublin Tel: +353 (0)1 466 6370 parker.ireland@parker.com

IN - India, Mumbai Tel: +91 22 6513 7081-85

IT – Italy, Corsico (MI) Tel: +39 02 45 19 21 parker.italy@parker.com

JP – Japan, Tokyo Tel: +(81) 3 6408 3900 infophj@parker.com

KR – South Korea, Seoul Tel: +82 2 559 0400 parkerkr@parker.com

KZ – Kazakhstan, Almaty Tel: +7 7272 505 800 parker.easteurope@parker.com

LV – Latvia, Riga Tel: +371 6 745 2601 parker.latvia@parker.com

MX - Mexico, Toluca Tel: +52 722 275 4200 contacto@parker.com

MY - Malaysia, Selangor Tel: +603 784 90 800 parkermy@parker.com

NL – The Netherlands, Oldenzaal Tel: +31 (0)541 585 000 parker.nl@parker.com

NO – Norway, Stavanger Tel: +47 (0)51 826 300 parker.norway@parker.com NZ – New Zealand, Mt Wellington

PL - Poland, Warsaw Tel: +48 (0)22 573 24 00 parker.poland@parker.com

PT - Portugal, Leca da Palmeira Tel: +351 22 999 7360 parker.portugal@parker.com

RO – Romania, Bucharest Tel: +40 21 252 1382 parker.romania@parker.com

RU – Russia, Moscow Tel: +7 495 645-2156 parker.russia@parker.com

SE – Sweden, Spånga Tel: +46 (0)8 59 79 50 00 parker.sweden@parker.com

SG – Singapore, Tel: +65 6887 6300 parkersg@parker.com

SK – Slovakia, Banská Bystrica Tel: +421 484 162 252 parker.slovakia@parker.com

SL – Slovenia, Novo Mesto Tel: +386 7 337 6650 parker.slovenia@parker.com

TH – Thailand, Bangkok Tel: +66 2 186 7000 phthailand@parker.com

TR – Turkey, Istanbul Tel: +90 216 4997081 parker.turkey@parker.com **TW** - Taiwan, Taipei Tel: +886 2 2298 8987 enquiry.taiwan@parker.com

UA – Ukraine, Kiev Tel: +380 44 494 2731 parker.ukraine@parker.com

UK – United Kingdom, Warwick Tel: +44 (0)1926 317878 parker.uk@parker.com

USA – IPD, Huntsville Tel: +1 256 881 2040 ipdcct@parker.com

USA – Autoclave Engineers, Erie Tel: +1 814 860 5700 ipdaecct@parker.com

VN - Vietnam, Hochi Minh City Tel: +84 (0)8337 546 51 parker_viet@parker.com

ZA – South Africa, Kempton Park Tel: +27 (0)11 961 0700 parker.southafrica@parker.com

WARNING

FAILURE, IMPROPER SELECTION OR IMPROPER USE OF THE PRODUCTS AND/OR SYSTEMS DESCRIBED HEREIN OR RELATED ITEMS CAN CAUSE DEATH, PERSONAL INJURY AND PROPERTY DAMAGE.

This document and other information from Parker Hannifin Corporation, its subsidiaries and authorized distributors provide product and/or system options for further investigation by users having technical expertise. It is important that you analyze all aspects of your application and review the information concerning the product or system in the current product catalog. Due to the variety of operating conditions and applications for these products or systems, the user, through its own analysis and testing, is solely responsible for making the final selection of the products and systems and assuring that all performance, safety and warning requirements of the application are met. The products described herein, including without limitation, product features, specifications, designs, availability and pricing, are subject to change by Parker Hannifin Corporation and its subsidiaries at any time without notice.

Offer of Sale

The items described in this document are available for sale by Parker Hannifin Corporation, its subsidiaries or its authorized distributors. Any sale contract entered by Parker will be governed by the provisions stated in Parker's standard terms and conditions of sale (copy available upon request).

© 2015 Parker Hannifin Corporation | Autoclave Engineers is a registered trademark of the Parker Hannifin Corporation

02-9326BE

May2015





Instrumentation Products Division

Autoclave Engineers Operation 8325 Hessinger Drive Erie, PA 16509-4679 Tel: 814 860 5700 Fax: 814 860 5811 www.autoclave.com **Instrumentation Products Division**

Autoclave Engineers Operation, Houston 15340 Vantage Parkway, East Houston, TX 77032 Tel: 281 987 3828 Fax: 281 987 2318 Parker Hannifin Manufacturing Ltd.

Instrumentation Products Division, Europe Industrial Estate Whitemill Wexford, Republic of Ireland Tel: 353 53 914 1566 Fax: 353 53 914 1582 Parker Hannifin Manufacturing Ltd.

Instrumentation Products Division, Europe Riverside Road, Pottington Business Park Barnstaple, UK, EX31 1NP, UK Tel: 44 1271 313131 Fax: 44 1271 373636

Caution! Do not mix or interchange component parts or tubing with those of other manufacturers. Doing so is unsafe and will void warranty.

Caution! Parker Autoclave Engineers Valves, Fittings, and Tools are not designed to interface with common commercial instrument tubing and are designed to only connect with tubing manufactured to Parker Autoclave Engineers AES specifications. Failure to do so is unsafe and will void warranty.