

	A	B	C	D	E	F
1		Persona - Inside Sales Curriculum				
2		Module Identifier	Overall Module List	Track A	Track B	Track C
3		CHOINTRO	Chomerics Video	A1		
4		FREQ101	The Frequency Spectrum	A2		
5		REGSTAN101	EMI/EMC Regulations and Standards		B1	
6		DESKINST	Applications Lab Desktop Instron			C1
7		EMIT101	EMI Theory		B2	
8		FILLERS101	Filler Technology - Therm & Elastomers			C2
9		CORR101	Corrosion			C3
10		RES101	Surface vs Volume Resistivity			C4
11		SE101	SE Primary Methods			C5
12		SE102	SE Secondary Methods			C6
13		SE103	SE Transfer Impedance Methods			C7
14		SE104	SE Cavity Isolation Methods			C8
15		EMP101	Electromagnetic Pulse (EMP)			C9
16		ABSORB101	Microwave Absorber Theory			C10
17		GASKETS101	General Gasket Type Selection	A3		
18		ELAS101	Elastomers - Material Selection	A4		
19		ELASTDS	Elements of a Elastomer Data Sheet	A5		
20		ELASSHAPE	Elastomer Shape Selection		B3	
21		ELAS102	Elastomer Gasket Design			C11
22		ELASNIAL	Nickel-Aluminum Gaskets		B4	
23		ELAS103	Elastomers Extrusion and Molding			C12
24		ELASFIP	Elastomer FIP Materials	A6		
25		TLSSS101	Soft Shield Gasket Materials	A7		
26		ME102	Fingerstock	A8		
27		ME103	Mesh/Metalastic/Pola	A9		
28		ME101	Vents	A10		
29		MEUM101	Urethane Metalastic		B5	
30		SPM101	Specialty Materials - Theory			C13
31		SPM102	Specialty Materials Coatings and Inks	A11		
32		SPM103	Specialty Materials - Cho-Shrink			C14
33		SPM104	Specialty Materials - Adhesives and Caulks	A12		
34		TLSTH101	Thermal General Theory			C15
35		TLSTDs	Elements of a Thermal Data Sheet	A13		
36		TLSPS101	Thermal Products Selection	A14		
37		TLSGEL	Thermal Gels	A15		
38		TLSGAPAD	Thermal Gap Pad Materials	A16		
39		TLSPHASE	Thermal Phase Change Materials		B6	
40		TLSTAPE	Thermal Double Sided Tapes Materials		B7	
41		TLSDIELEC	Thermal Dielectric Pad Materials		B8	
42		TLSPOT	Thermal Potting Compound Materials		B9	
43		TLSGREASE	Thermal Grease Materials			C16
44		TLSSPREAD	Thermal Heat Spreaders			C17
45		TLSTM101	Thermal Test Methods			C18
46		TD101	Therm Dispense #1			C19
47		IDS101	Integrated Display Solutions	A17		