

UNIFORM STATUTORY DECLARATION FORM FOR THE REGISTRATION OF FITTING DESIGNS

NEW BRUNSWICK
NUNAVUTNOVA SCOTIA
YUKONPRINCE EDWARD ISLAND
NORTHWEST TERRITORIES

NEWFOUNDLAND AND LABRADOR

MANUFACTURERS NAME: PARKER HANNIFIN IPDE

MANUFACTURERS ADDRESS: RIVERSIDE ROAD, BARNSTAPLE, DEVON, UK EX31 1NP

PLANT LOCATIONS: AS ABOVE

CATEGORY OF FITTINGS TO BE REGISTERED. CIRCLE ONE CATEGORY ONLY

- A Pipe fittings, including couplings, tees, elbows, Ys, plugs, unions, pipe caps, or reducers
 B Flanges: all flanges
 C Valves: all line valves
 D Expansion joints, flexible connections, and hose assemblies: all types
 E Strainers, filters, separators, and steam traps
 F Measuring devices, including pressure gauges, level gauges, sight glasses, levels, or pressure transmitters
 G Certified capacity-rated pressure relief devices acceptable as primary over pressure protection on boilers, pressure vessels, piping and fusible plugs
 H Pressure retaining components that do not fall into one of the above categories
 N Nuclear components: Class 1 ☐ Class 2 ☐ Class 3 ☐ (Meeting AECB or ASME requirements)

TITLE OF THE STANDARD OF CONSTRUCTION

MSS SP99
 ASME B31.1
 ASME B31.3
 ASME B16.5
 ASME B16.34
 ASME VIII
 FED-STD-H28/2B

SHOW MANUFACTURERS NAME, TRADEMARK, OR LOGO AS IT WILL APPEAR ON THE PRODUCT



TYPE OF CONSTRUCTION

FORGED ☒ WELDED ☐ WROUGHT ☒
 CAST ☐ OTHER ☐
 DESCRIBE OTHER:
 BODY=FORGED
 COMPONENTS=WROUGHT BAR

LIST OF SUPPORTING DOCUMENTATION AND IDENTIFICATION OF THE ACTUAL ITEMS TO BE REGISTERED:

CATALOG 4190-FP
 CS-DUP-PROBLOC-S-10-CRN-CALC REV1

DECLARATION:

I JAMES NELSON (see note 3) employed by PARKER and being the person having full authority and responsibility for the quality of the end product do solemnly declare that the information contained in this form is true and to the best of my knowledge represents the product for which registration is sought. The dimensions, materials of construction, pressure temperature ratings, and identification markings are in accordance with the herein named standards. I further declare that the manufacture of these fittings is regulated by a Quality Control Program which extends to each plant where fabrication occurs in whole or in part and has been verified by DNV MANAGEMENT SYSTEM as being suitable for that purpose and I make this solemn declaration conscientiously believing it to be true, and knowing that it is of the same force and effect as if made under oath.

Signature of Declarer:

Declared before me at

This 18th day ofAD 2017Commissioner of Oaths
or Notary Public: (sign)

(Affix Official seal to the right)

USE THIS SPACE FOR THE
OFFICIAL SEAL


This space for Regulatory Authority use

This registration must be revalidated after ten (10) years from the date of acceptance.

CRN: OC19249.5FID#: 2655

Notes:

1. All fittings shall be registered in the name of the Manufacturer.
2. Each category shall be supported with two Statutory Declaration forms and one copy of supporting documentation.
3. The declaration shall be made by the person having full authority and responsibility for the quality of the end product.
4. Quality control programs shall be resubmitted for validation at a maximum interval of five (5) years.



UNIFORM STATUTORY DECLARATION FORM FOR THE REGISTRATION OF FITTING DESIGNS

NEW BRUNSWICK
NUNAVUT

NOVA SCOTIA
YUKON

PRINCE EDWARD ISLAND
NORTHWEST TERRITORIES

NEWFOUNDLAND AND LABRADOR

MANUFACTURERS NAME: PARKER HANNIFIN IPDE

MANUFACTURERS ADDRESS: RIVERSIDE ROAD, BARNSTAPLE, DEVON, UK EX31 1NP

PLANT LOCATIONS: AS ABOVE

CATEGORY OF FITTINGS TO BE REGISTERED. CIRCLE ONE CATEGORY ONLY

- A Pipe fittings, including couplings, tees, elbows, Ys, plugs, unions, pipe caps, or reducers
 B Flanges: all flanges
 C Valves: all line valves
 D Expansion joints, flexible connections, and hose assemblies: all types
 E Strainers, filters, separators, and steam traps
 F Measuring devices, including pressure gauges, level gauges, sight glasses, levels, or pressure transmitters
 G Certified capacity-rated pressure relief devices acceptable as primary over pressure protection on boilers, pressure vessels, piping and fusible plugs
 H Pressure retaining components that do not fall into one of the above categories
 N Nuclear components: Class 1 ☐ Class 2 ☐ Class 3 ☐ (Meeting AECB or ASME requirements)

TITLE OF THE STANDARD OF CONSTRUCTION

MSS SP99
 ASME B31.1
 ASME B31.3
 ASME B16.5
 ASME B16.34
 ASME VIII
 FED-STD-H28/2B

SHOW MANUFACTURERS NAME, TRADEMARK, OR LOGO AS IT WILL APPEAR ON THE PRODUCT



TYPE OF CONSTRUCTION

FORGED ☒ WELDED ☐ WROUGHT ☒
 CAST ☐ OTHER ☐
 DESCRIBE OTHER:
 BODY=FORGED
 COMPONENTS=WROUGHT BAR

LIST OF SUPPORTING DOCUMENTATION AND IDENTIFICATION OF THE ACTUAL ITEMS TO BE REGISTERED:

CATALOG 4190-FP
 PROBLOC-10-CRN-CALC REV2

DECLARATION:

I, JAMES NELSON (see note 3) employed by PARKER and being the person having full authority and responsibility for the quality of the end product do solemnly declare that the information contained in this form is true and to the best of my knowledge represents the product for which registration is sought. The dimensions, materials of construction, pressure temperature ratings, and identification markings are in accordance with the herein named standards. I further declare that the manufacture of these fittings is regulated by a Quality Control Program which extends to each plant where fabrication occurs in whole or in part and has been verified by DNV MANAGEMENT SYSTEMS as being suitable for that purpose and I make this solemn declaration conscientiously believing it to be true, and knowing that it is of the same force and effect as if made under oath.

Signature of Declarer: J. P. Nelson

Declared before me at Bridgetown, Barbados

This 16th day of April AD 2017

Commissioner of Oaths
 or Notary Public: (sign) [Signature]

(Affix Official seal to the right)

USE THIS SPACE FOR THE
 OFFICIAL SEAL

This space for Regulatory Authority use


This registration must be revalidated after ten (10) years from the date of acceptance.

CRN: 0C19249.5

FID#: 2655

Notes:

- All fittings shall be registered in the name of the Manufacturer.
- Each category shall be supported with two Statutory Declaration forms and one copy of supporting documentation.
- The declaration shall be made by the person having full authority and responsibility for the quality of the end product.
- Quality control programs shall be resubmitted for validation at a maximum interval of five (5) years.




UNIFORM STATUTORY DECLARATION FORM FOR THE REGISTRATION OF FITTING DESIGNS

NEW BRUNSWICK
NUNAVUT

NOVA SCOTIA
YUKON

PRINCE EDWARD ISLAND
NORTHWEST TERRITORIES

NEWFOUNDLAND AND LABRADOR

MANUFACTURERS NAME: PARKER HANNIFIN IPDE	
MANUFACTURERS ADDRESS: RIVERSIDE ROAD, BARNSTAPLE, DEVON, UK EX31 1NP	
PLANT LOCATIONS: AS ABOVE	
CATEGORY OF FITTINGS TO BE REGISTERED. CIRCLE ONE CATEGORY ONLY A Pipe fittings, including couplings, tees, elbows, Ys, plugs, unions, pipe caps, or reducers B Flanges: all flanges C Valves: all line valves D Expansion joints, flexible connections, and hose assemblies: all types E Strainers, filters, separators, and steam traps F Measuring devices, including pressure gauges, level gauges, sight glasses, levels, or pressure transmitters G Certified capacity-rated pressure relief devices acceptable as primary over pressure protection on boilers, pressure vessels, piping and fusible plugs H Pressure retaining components that do not fall into one of the above categories N Nuclear components: Class 1 <input type="checkbox"/> Class 2 <input type="checkbox"/> Class 3 <input type="checkbox"/> (Meeting AECS or ASME requirements)	
TITLE OF THE STANDARD OF CONSTRUCTION MSS SP99 ASME B31.1 ASME B31.3 ASME B16.5 ASME B16.34 ASME VIII FED-STD-H28/2B	
SHOW MANUFACTURERS NAME, TRADEMARK, OR LOGO AS IT WILL APPEAR ON THE PRODUCT 	
TYPE OF CONSTRUCTION FORGED <input checked="" type="checkbox"/> WELDED <input type="checkbox"/> WROUGHT <input checked="" type="checkbox"/> CAST <input type="checkbox"/> OTHER <input type="checkbox"/> DESCRIBE OTHER: BODY=FORGED COMPONENTS=WROUGHT BAR	
LIST OF SUPPORTING DOCUMENTATION AND IDENTIFICATION OF THE ACTUAL ITEMS TO BE REGISTERED: CATALOG 4190-FP DESIGN VERIFICATION MONOFLANGE DATED 21/03/2007	

DECLARATION:

I, JAMES NASON (see note 3) employed by Parker and being the person having full authority and responsibility for the quality of the end product do solemnly declare that the information contained in this form is true and to the best of my knowledge represents the product for which registration is sought. The dimensions, materials of construction, pressure temperature ratings, and identification markings are in accordance with the herein named standards. I further declare that the manufacture of these fittings is regulated by a Quality Control Program which extends to each plant where fabrication occurs in whole or in part and has been verified by QMS MANAGEMENT SYSTEM as being suitable for that purpose and I make this solemn declaration conscientiously believing it to be true, and knowing that it is of the same force and effect as if made under oath.

Signature of Declarer: J. Nason


Declared before me at Richmond upon Thames

This 1st day of April 2017

Commissioner of Oaths
or Notary Public: (sign) [Signature]

(Affix Official seal to the right)

USE THIS SPACE FOR THE
OFFICIAL SEAL

This space for Regulatory Authority use This registration must be revalidated after ten (10) years from the date of acceptance.	
CRN: <u>OC19249.5</u>	 BOILER & PRESSURE VESSEL NOVA SCOTIA Date <u>April 21/17</u> C.R.N. <u>OC19249.58</u> Dwg. <u>as described</u> Signed <u>Yvonne Perry</u> <u>1 of 1</u> Part ACT & REGULATIONS
FID#: <u>2655</u>	
Notes:	
1. All fittings shall be registered in the name of the Manufacturer. 2. Each category shall be supported with two Statutory Declaration forms and one copy of supporting documentation. 3. The declaration shall be made by the person having full authority and responsibility for the quality of the end product. 4. Quality control programs shall be resubmitted for validation at a maximum interval of five (5) years.	

UNIFORM STATUTORY DECLARATION FORM FOR THE REGISTRATION OF FITTING DESIGNS

NEW BRUNSWICK
NUNAVUT

NOVA SCOTIA
YUKON

PRINCE EDWARD ISLAND
NORTHWEST TERRITORIES

NEWFOUNDLAND AND LABRADOR

MANUFACTURERS NAME: PARKER HANNIFIN IPDE

MANUFACTURERS ADDRESS: RIVERSIDE ROAD, BARNSTAPLE, DEVON, UK EX31 1NP

PLANT LOCATIONS: AS ABOVE

CATEGORY OF FITTINGS TO BE REGISTERED. CIRCLE ONE CATEGORY ONLY

- A Pipe fittings, including couplings, tees, elbows, Ys, plugs, unions, pipe caps, or reducers
 B Flanges: all flanges
 C Valves: all line valves
 D Expansion joints, flexible connections, and hose assemblies: all types
 E Strainers, filters, separators, and steam traps
 F Measuring devices, including pressure gauges, level gauges, sight glasses, levels, or pressure transmitters
 G Certified capacity-rated pressure relief devices acceptable as primary over pressure protection on boilers, pressure vessels, piping and fusible plugs
 H Pressure retaining components that do not fall into one of the above categories
 N Nuclear components: Class 1 ☐ Class 2 ☐ Class 3 ☐ (Meeting AECB or ASME requirements)

TITLE OF THE STANDARD OF CONSTRUCTION

MSS SP99
 ASME B31.1
 ASME B31.3
 ASME B16.5
 ASME B16.34
 ASME VIII
 FED-STD-H28/2B

SHOW MANUFACTURERS NAME, TRADEMARK, OR LOGO AS IT WILL APPEAR ON THE PRODUCT



TYPE OF CONSTRUCTION

FORGED ☒ WELDED ☐ WROUGHT ☒
 CAST ☐ OTHER ☐
 DESCRIBE OTHER:
 BODY=FORGED
 COMPONENTS=WROUGHT BAR

LIST OF SUPPORTING DOCUMENTATION AND IDENTIFICATION OF THE ACTUAL ITEMS TO BE REGISTERED:

CATALOG 4190-FP
 DESIGN VERIFICATION MONOFLANGE DATED 21/03/2007
 MONOFLANGE 1/2"-2" FLANGE CONNECTIONS A105, A182-F51-F53, A182-F316, B564 N04400, B564 N10276, A182 F44, A182 F316

DECLARATION:

I, JAMES NELSON (see note 3) employed by PARKER and being the person having full authority and responsibility for the quality of the end product do solemnly declare that the information contained in this form is true and to the best of my knowledge represents the product for which registration is sought. The dimensions, materials of construction, pressure temperature ratings, and identification markings are in accordance with the herein named standards. I further declare that the manufacture of these fittings is regulated by a Quality Control Program which extends to each plant where fabrication occurs in whole or in part and has been verified by QMS MANAGEMENT SYSTEM as being suitable for that purpose and I make this solemn declaration conscientiously believing it to be true, and knowing that it is of the same force and effect as if made under oath.

Signature of Declarer: J. P. Nelson

Declared before me at Bedford Park, Nova Scotia

This 18th day of January AD 2017

Commissioner of Oaths
 or Notary Public: (sign) [Signature]

(Affix Official seal to the right)

USE THIS SPACE FOR THE
 OFFICIAL SEAL

This space for Regulatory Authority use


This registration must be revalidated after ten (10) years from the date of acceptance.

CRN: OC19249.5

FID#: 2655

Notes:

- All fittings shall be registered in the name of the Manufacturer.
- Each category shall be supported with two Statutory Declaration forms and one copy of supporting documentation.
- The declaration shall be made by the person having full authority and responsibility for the quality of the end product.
- Quality control programs shall be resubmitted for validation at a maximum interval of five (5) years.



UNIFORM STATUTORY DECLARATION FORM FOR THE REGISTRATION OF FITTING DESIGNS

NEW BRUNSWICK
NEWFOUNDLAND

NOVA SCOTIA
YUKON

PRINCE EDWARD ISLAND
NORTHWEST TERRITORIES

NEWFOUNDLAND AND LABRADOR

MANUFACTURERS NAME: PARKER HANNIFIN IPDE

MANUFACTURERS ADDRESS: RIVERSIDE ROAD, BARNSTAPLE, DEVON, UK EX31 1NP

PLANT LOCATIONS: AS ABOVE

CATEGORY OF FITTINGS TO BE REGISTERED. CIRCLE ONE CATEGORY ONLY

A Pipe fittings, including couplings, tees, elbows, Ys, plugs, unions, pipe caps, or reducers

B Flanges: all flanges

C Valves: all line valves

D Expansion joints, flexible connections, and hose assemblies: all types

E Strainers, filters, separators, and steam traps

F Measuring devices, including pressure gauges, level gauges, sight glasses, levels, or pressure transmitters

G Certified capacity-rated pressure relief devices acceptable as primary over pressure protection on boilers, pressure vessels, piping and fusible plugs

H Pressure retaining components that do not fall into one of the above categories

N Nuclear components: Class 1 ☐ Class 2 ☐ Class 3 ☐ (Meeting AECB or ASME requirements)

TITLE OF THE STANDARD OF CONSTRUCTION

MSS SP99

ASME B31.1

ASME B31.3

ASME B16.5

ASME B16.34

ASME VIII

FED-STD-H28/2B

SHOW MANUFACTURERS NAME, TRADEMARK, OR LOGO AS IT WILL APPEAR ON THE PRODUCT



TYPE OF CONSTRUCTION

FORGED ☒ WELDED ☐ WROUGHT ☒
CAST ☐ OTHER ☐

DESCRIBE OTHER:

BODY=FORGED

COMPONENTS=WROUGHT BAR

LIST OF SUPPORTING DOCUMENTATION AND IDENTIFICATION OF THE ACTUAL ITEMS TO BE REGISTERED:

CATALOG 4190-FP WITH THE ADDITION OF 3" RF/RTJ 150# TO 2500# DESIGN CALC (MONO-CRN-CALC ADD1 REV1)
DESIGN VERIFICATION MONOFLANGE DATED 21/03/2007

DECLARATION:

I, JAMES NELSON (see note 3) employed by Parker and being the person having full authority and responsibility for the quality of the end product do solemnly declare that the information contained in this form is true and to the best of my knowledge represents the product for which registration is sought. The dimensions, materials of construction, pressure temperature ratings, and identification markings are in accordance with the herein named standards. I further declare that the manufacture of these fittings is regulated by a Quality Control Program which extends to each plant where fabrication occurs in whole or in part and has been verified by DNV MANAGEMENT SYSTEM as being suitable for that purpose and I make this solemn declaration conscientiously believing it to be true, and knowing that it is of the same force and effect as if made under oath.

Signature of Declarer: J. P. Nelson

Declared before me at Richmond, Nova Scotia

This 16th day of January AD 2014

Commissioner of Oaths
or Notary Public: (sign) [Signature]

(Affix Official seal to the right)

USE THIS SPACE FOR THE
OFFICIAL SEAL

This space for Regulatory Authority use

This registration must be revalidated after ten (10) years from the date of acceptance.

CRN: OC19249.5

FID#: 2655

Notes:

1. All fittings shall be registered in the name of the Manufacturer.
2. Each category shall be supported with two Statutory Declaration forms and one copy of supporting documentation.
3. The declaration shall be made by the person having full authority and responsibility for the quality of the end product.
4. Quality control programs shall be resubmitted for validation at a maximum interval of five (5) years.

