

UNIFORM STATUTORY DECLARATION FORM FOR THE REGISTRATION OF FITTING DESIGNS

New Brunswick
Nunavut

Nova Scotia
Yukon

Prince Edward Island
Northwest Territories

Newfoundland and Labrador

Manufacturers Name: Parker Hannifin Manufacturing France SAS	
Manufacturers Address: 1 rue André et Yvonne Meynier - 35069 RENNES CEDEX	
Plant Locations: rennes	
<p>Category of Fittings to be registered. Circle one Category only</p> <p><input type="checkbox"/> A Pipe fittings, including couplings, tees, elbows, Ys, plugs, unions, pipe caps, or reducers</p> <p><input type="checkbox"/> B Flanges: all flanges</p> <p><input checked="" type="checkbox"/> C Valves: all line valves</p> <p><input type="checkbox"/> D Expansion joints, flexible connections, and hose assemblies: all types</p> <p><input type="checkbox"/> E Strainers, filters, separators, and steam traps</p> <p><input type="checkbox"/> F Measuring devices, including pressure gauges, level gauges, sight glasses, levels, or pressure transmitters</p> <p><input type="checkbox"/> G Certified capacity-rated pressure relief devices acceptable as primary over pressure protection on boilers, pressure vessels, piping and fusible plugs</p> <p><input type="checkbox"/> H Pressure retaining components that do not fall into one of the above categories</p> <p><input type="checkbox"/> N Nuclear components: Class 1 <input type="checkbox"/> Class 2 <input type="checkbox"/> Class 3 <input type="checkbox"/> (Meeting CNSC or ASME requirements)</p>	<p>Title of the Standard of Construction</p> <p>ASME B31.1 (non-boiler external piping) & ASME B31.3</p>
<p>Show Manufacturers Name, Trademark, or Logo as it will appear on the product</p> <p align="center">TRANSAIR</p>	
<p>Type of Construction</p> <p>Forged <input type="checkbox"/> Welded <input type="checkbox"/> Wrought <input type="checkbox"/></p> <p>Cast <input type="checkbox"/> Other <input type="checkbox"/></p> <p>Describe other:</p>	
<p>List of supporting documentation and identification of the actual items to be registered:</p> <p>Ø 2" TRANSAIR range :</p> <ul style="list-style-type: none"> - fitting drawings - proof test reports - ISO 9001 certificate - range presentation 	

Declaration:

I, Chantal BECKENSTEINER (see note 3) employed by Parker Hannifin and being the person having full authority and responsibility for the quality of the end product do solemnly declare that the information contained in this form is true to the best of my knowledge represents the product for which registration is sought. The dimensions, materials of construction, pressure temperature ratings, and identification markings are in accordance with the herein named standards. I further declare that the manufacture of these fittings is regulated by a Quality Control Program which extends to each plant where fabrication occurs in whole or in part and has been verified by afsa as being suitable for that purpose and I make this solemn declaration conscientiously believing it to be true, and knowing that it is of the same force and effect as if made under oath.

Signature of Declarer: _____

Declared before me at _____

This 6th day of November AD 2018

Commissioner of Oaths

Or Notary Public: (sign) M^e LATRILLE

(Affix Official seal to the right)

Use this space for the Official Seal



<p>CRN: <u>QC15761.5 ADD1</u></p> <p>FID#: <u>15817</u></p> <p>Notes:</p> <ol style="list-style-type: none"> 1. All Fittings shall be registered in the name of the Manufacturer. 2. Each Category shall be supported with two Statutory Declaration forms and one copy of supporting documentation. 3. The Declaration shall be made by the person having full authority and responsibility for the quality of the end product. 4. Quality Control programs shall be resubmitted for validation. <p>11/2018</p> <p>CRN EXPIRES JAN. 21, 2023 - D.B.</p>	<p align="center">This space for Regulatory Authority use.</p> <p align="center">This registration must be revalidated after ten (10) years from the date of issuance.</p> <p align="center">ACCEPTED</p> <p align="center">PROVINCE OF PRINCE EDWARD ISLAND</p> <p align="center">COMMUNITIES, LAND & ENVIRONMENT</p> <p>C.R.N. <u>QC15761.59 ADD1</u></p> <p>DATE: <u>July 26 2019</u></p> <p><u>Jerry McGowan</u></p> <p align="center">INSPECTION SERVICES SECTION</p> <p align="center">BOILER/PRESSURE VESSEL BRANCH</p> <p align="right">Sect 1.0 - Fittings Rev.2</p>
---	--

UNIFORM STATUTORY DECLARATION FORM FOR THE REGISTRATION OF FITTING DESIGNS

New Brunswick
Nunavut

Nova Scotia
Yukon

Prince Edward Island
Northwest Territories

Newfoundland and Labrador

Manufacturers Name: Parker Hannifin Manufacturing France SAS	
Manufacturers Address: 1 rue André et Yvonne Meynier - 35069 RENNES CEDEX	
Plant Locations: rennes	
<p>Category of Fittings to be registered. Circle one Category only</p> <p><input type="checkbox"/> Pipe fittings, including couplings, tees, elbows, Ys, plugs, unions, pipe caps, or reducers</p> <p><input type="checkbox"/> Flanges: all flanges</p> <p><input checked="" type="checkbox"/> Valves: all line valves</p> <p><input type="checkbox"/> Expansion joints, flexible connections, and hose assemblies: all types</p> <p><input type="checkbox"/> Strainers, filters, separators, and steam traps</p> <p><input type="checkbox"/> Measuring devices, including pressure gauges, level gauges, sight glasses, levels, or pressure transmitters</p> <p><input type="checkbox"/> Certified capacity-rated pressure relief devices acceptable as primary over pressure protection on boilers, pressure vessels, piping and fusible plugs</p> <p><input type="checkbox"/> Pressure retaining components that do not fall into one of the above categories</p> <p><input type="checkbox"/> Nuclear components: Class 1 <input type="checkbox"/> Class 2 <input type="checkbox"/> Class 3 <input type="checkbox"/> (Meeting CNSC or ASME requirements)</p>	<p>Title of the Standard of Construction</p> <p>ASME B31.1 1 (non-boiler external piping) & ASME B31.3</p>
<p>Show Manufacturers Name, Trademark, or Logo as it will appear on the product</p> <p align="center">TRANSAIR</p>	<p>Type of Construction</p> <p>Forged <input type="checkbox"/> Welded <input type="checkbox"/> Wrought <input type="checkbox"/></p> <p>Cast <input type="checkbox"/> Other <input type="checkbox"/></p> <p>Describe other:</p>
<p>List of supporting documentation and identification of the actual items to be registered:</p> <p>Ø 2" TRANSAIR range :</p> <ul style="list-style-type: none"> - fitting drawings - proof test reports - ISO 9001 certificate - range presentation 	

Declaration:

I Chantal BECKENSTEINER (see note 3) employed by Parker Hannifin and being the person having full authority and responsibility for the quality of the end product do solemnly declare that the information contained in this form is true to the best of my knowledge represents the product for which registration is sought. The dimensions, materials of construction, pressure temperature ratings, and identification markings are in accordance with the herein named standards. I further declare that the manufacture of these fittings is regulated by a Quality Control Program which extends to each plant where fabrication occurs in whole or in part and has been verified by me as being suitable for that purpose and I make this solemn declaration conscientiously believing it to be true, and knowing that it is of the same force and effect as if made under oath.

Signature of Declarer: _____

Declared before me at RENNES (FRANCE)


This 6th day of November AD 2018

Use this space for the Official Seal

Commissioner of Oaths

Or Notary Public: (sign) M^e LATRILLE

(Affix Official seal to the right)



This space for Regulatory Authority use.

This registration must be revalidated after ten (10) years from the date of acceptance.

CRN: OC15761.5 ADD1


FID#: 15817

Notes:

1. All Fittings shall be registered in the name of the Manufacturer.
2. Each Category shall be supported with two Statutory Declaration forms and one copy of supporting documentation.
3. The Declaration shall be made by the person having full authority and responsibility for the quality of the end product.
4. Quality Control programs shall be resubmitted for validation.

11/2018

CRN EXPIRES JAN.21,2023-D6.



Date July 26/19

C.R.N. OC15761.58ADD1

Dwg. as described

Signed Yvonne Perry

1 of 1

Part



Sect 1.0 - Fittings Rev.2

UNIFORM STATUTORY DECLARATION FORM FOR THE REGISTRATION OF FITTING DESIGNS

New Brunswick
Nunavut

Nova Scotia
Yukon

Prince Edward Island
Northwest Territories

Newfoundland and Labrador

Manufacturers Name: Parker Hannifin Manufacturing France SAS

Manufacturers Address: 1 rue André et Yvonne Meynier - 35069 RENNES CEDEX

Plant Locations: rennes

Category of Fittings to be registered. Circle one Category only

- ☐ Pipe fittings, including couplings, tees, elbows, Ys, plugs, unions, pipe caps, or reducers
☐ Flanges: all flanges
☒ Valves: all line valves
☐ Expansion joints, flexible connections, and hose assemblies: all types
☐ Strainers, filters, separators, and steam traps
☐ Measuring devices, including pressure gauges, level gauges, sight glasses, levels, or pressure transmitters
☐ Certified capacity-rated pressure relief devices acceptable as primary over pressure protection on boilers, pressure vessels, piping and fusible plugs
☐ Pressure retaining components that do not fall into one of the above categories
☐ Nuclear components: Class 1 ☐ Class 2 ☐ Class 3 ☐ (Meeting CNSC or ASME requirements)

Title of the Standard of Construction

ASME B31.1 1 (non-boiler external piping) & ASME B31.3

Show Manufacturers Name, Trademark, or Logo as it will appear on the product

TRANSAIR

Type of Construction

Forged ☐ Welded ☐ Wrought ☐
 Cast ☐ Other ☐
 Describe other:

List of supporting documentation and identification of the actual items to be registered:

Ø 2" TRANSAIR range :

- fitting drawings
- proof test reports
- ISO 9001 certificate
- range presentation

Declaration:

I Chantal BECKENSTEINER (see note 3) employed by Parker Hannifin and being the person having full authority and responsibility for the quality of the end product do solemnly declare that the information contained in this form is true to the best of my knowledge represents the product for which registration is sought. The dimensions, materials of construction, pressure temperature ratings, and identification markings are in accordance with the herein named standards. I further declare that the manufacture of these fittings is regulated by a Quality Control Program which extends to each plant where fabrication occurs in whole or in part and has been verified by afeq as being suitable for that purpose and I make this solemn declaration conscientiously believing it to be true, and knowing that it is of the same force and effect as if made under oath.

Signature of Declarer: [Signature]

Declared before me at RENNES (FRANCE)

This 6th day of November AD 2018

Commissioner of Oaths

Or Notary Public: (sign) M^e LATRILLE

(Affix Official seal to the right)

Use this space for the Official Seal
Brunswick
 DEPT OF JUSTICE - PUBLIC SAFETY
 BOILER & PRESSURE VESSEL ACT

This space for Regulatory Authority use.

This registration must be revalidated after ten (10) years from the date of acceptance.

CRN: OC15761.5 ADD1

FID#: 15817

Notes:

1. All Fittings shall be registered in the name of the Manufacturer.
2. Each Category shall be supported with two Statutory Declaration forms and one copy of supporting documentation.
3. The Declaration shall be made by the person having full authority and responsibility for the quality of the end product.
4. Quality Control programs shall be resubmitted for validation.

11/2016

CRN EXPIRES JAN. 21, 2023 - D.B.

REGISTRATION ONLY

CRN OC15761.57Add1

[Signature]
 CHIEF BOILER INSPECTOR

DATE 7/26/2019

☐ BLRs

☐ PVs

Sect 1.0 - Fittings Rev.2

☐ FITTINGS

☐ NUCLEAR COMPONENTS

UNIFORM STATUTORY DECLARATION FORM FOR THE REGISTRATION OF FITTING DESIGNS

New Brunswick
Nunavut

Nova Scotia
Yukon

Prince Edward Island
Northwest Territories

Newfoundland and Labrador

Manufacturers Name: Parker Hannifin Manufacturing France SAS

Manufacturers Address: 1 rue André et Yvonne Meynier - 35069 RENNES CEDEX

Plant Locations: rennes

Category of Fittings to be registered. Circle one Category only

- ☐ Pipe fittings, including couplings, tees, elbows, Ys, plugs, unions, pipe caps, or reducers
☐ Flanges: all flanges
☒ Valves: all line valves
☐ Expansion joints, flexible connections, and hose assemblies: all types
☐ Strainers, filters, separators, and steam traps
☐ Measuring devices, including pressure gauges, level gauges, sight glasses, levels, or pressure transmitters
☐ Certified capacity-rated pressure relief devices acceptable as primary over pressure protection on boilers, pressure vessels, piping and fusible plugs
☐ Pressure retaining components that do not fall into one of the above categories
☐ Nuclear components: Class 1 ☐ Class 2 ☐ Class 3 ☐ (Meeting CNSC or ASME requirements)

Show Manufacturers Name, Trademark, or Logo as it will appear on the product

TRANSAIR

Title of the Standard of Construction

ASME B31.1 1 (non-boiler external piping) & ASME B31.3

Type of Construction

Forged ☐ Welded ☐ Wrought ☐
 Cast ☐ Other ☐
 Describe other:

List of supporting documentation and identification of the actual items to be registered:

- Ø 2" TRANSAIR range :
 - fitting drawings
 - proof test reports
 - ISO 9001 certificate
 - range presentation

Declaration:

I Chantal BECKENSTEINER (see note 3) employed by Parker Hannifin and being the person having full authority and responsibility for the quality of the end product do solemnly declare that the information contained in this form is true to the best of my knowledge represents the product for which registration is sought. The dimensions, materials of construction, pressure temperature ratings, and identification markings are in accordance with the herein named standards. I further declare that the manufacture of these fittings is regulated by a Quality Control Program which extends to each plant where fabrication occurs in whole or in part and has been verified by afec as being suitable for that purpose and I make this solemn declaration conscientiously believing it to be true, and knowing that it is of the same force and effect as if made under oath.

Signature of Declarer: _____


Declared before me at _____

This 6th day of November AD 2018

Commissioner of Oaths

Or Notary Public: (sign) M^e LATRILLE

(Affix Official seal to the right)



This space for Regulatory Authority use.

This registration must be revalidated after ten (10) years from the date of acceptance.

CRN: 0C15761.5 ADD1

FID#: 15817

Notes:

- All Fittings shall be registered in the name of the Manufacturer.
- Each Category shall be supported with two Statutory Declaration forms and one copy of supporting documentation.
- The Declaration shall be made by the person having full authority and responsibility for the quality of the end product.
- Quality Control programs shall be resubmitted for validation.

11/2016

CRN EXPIRES JAN. 21, 2023 - D.B.

Newfoundland
Labrador
Service NL

Registered 0C15761.50 ADD.1
 Date 19/07/2019

Engineering and Inspection Services

Registered by [Signature]
 UNDER THE AUTHORITY OF THE
 PUBLIC SAFETY ACT Rev.2
 THE BOILER, PRESSURE VESSEL AND
 COMPRESSED GAS REGULATIONS