



the pressure equipment safety authority

9410 - 20 Ave N.W.
Edmonton, Alberta, Canada T6N 0A4
Tel: (780) 437-9100 / Fax: (780) 437-7787

March 28, 2016

Attention: Scott Lehman
PARKER HANNIFIN CORPORATION
HYDRAULIC FILTER DIVISION
16810 FULTON CR2
METAMORA, OH 43540

The design submission, tracking number 2016-00384, originally received on January 20, 2016 was surveyed and accepted for registration as follows:

CRN : 0H16737.2 **Accepted on:** March 28, 2016
Reg Type: New Design **Expiry Date:** March 28, 2026
Drawing No. : 929255 REV L, 933882 REV E, 933391 REV G, 733568 REV E As Noted
Fitting type: FITTING HOUSING

| Description | MAWP | Design Temperature | MDMT |
|-------------------|---------|--------------------|--------|
| Internal Pressure | 6895kPa | 107 °C | -26 °C |

The registration is conditional on your compliance with the following notes:

The filter shall be hydrotested at minimum of 1500 psig.

It is our understanding that the complete filter housing is constructed with aluminum casting ASTM B26 Gr.356 T6.

Please note filter housing for hydraulic fluid service is neither required nor recommended for registration because the Safety Codes Act & Regulations will apply to equipment for expansible fluid service only.

This registration is valid only for fittings fabricated at the location(s) covered by the QC certificate attached to the accepted AB-41 Statutory Declaration form. This registration is valid only until the indicated expiry date only if the Manufacturer maintains a valid quality management system approved by an acceptable third-party agency until that date. Should the approval of the quality management system lapse before the expiry date indicated above, this registration shall become void.

An invoice covering survey and registration fees will be forwarded from our Revenue Accounts.

If you have any question don't hesitate to contact me by phone at (780) 433-0281 ext 3369 or fax (780) 437-7787 or e-mail Radisavljevic@absa.ca.

Sincerely,

RADISAVLJEVIC, ZANA, R.E.T.