

SALES TIPS

LF 3800 Push-In Fittings



1

Robust for Aggressive Environments

- **Full metal design** in the best **316L** stainless steel, for extreme resistance to external and internal fluids
- High **temperature** resistance (up to + 150 °C) and large **chemical compatibility** with FKM seals
- High **vibration & pressure resistance**, up to 30 bar, thanks to the collet gripping technology
- Perfect fittings for **food, chemical & medical** applications

2

Safe & Reliable for Peace of Mind

- **Fluid integrity** thanks to 316L stainless steel material
- Unique **hygienic external design** facilitating cleaning process and avoiding any contamination: smooth surface (Ra 0,8) and no retention zone
- Proven **automated** process which is camera **controlled**
- 100% leak test control
- **Quality Management** system that follows ISO IATF 16949 automotive industry requirements
- Products **made in Europe** to ensure a sustainable service