

SALES TIPS

LIQUIfit® with Metal Adaptor



1

Specifically Designed for Liquids

2

Reliable for Peace of Mind

- Compliant with the most demanding **food & beverage regulations** (NSF, FDA, ACS, WRAS, 1935/2004, DM 174, KTW for stainless steel only)
- **Higher sealing performance** thanks to the lowest pumping effect on the market (0,2 mm only)
- **Compact** product: 20%-40% more compact than competitors
- Proven **automated** process which is camera **controlled**
- 100% leak test control
- Strong quality management system: **ISO 16949 IATF** automotive industry certification
- Products **made in Europe** to ensure a sustainable service

3

Robust for Demanding Applications

- Strong mechanical resistance at **high temperature** (+ 130°C and 10 bar) for Ø 4, 6 and 8 mm
- High resistance to **agressive environment** with the **316L stainless steel** adaptor, meet the food & beverage industry requirements
- **Nickel-plated brass** version offers a good alternative for **industrial fluids** applications

4

Safe for Users' Protection

- **Bisphenol and phthalate-free**
- **No substances migration** for perfect fluid integrity with bio-based engineered polymer

5

Safe for Environmental Concern

- **Sustainable** product using bio-based polymer
- Generate **5 times less CO₂** during its life cycle