

SALES TIPS

LIQUIfit® Push-In Fittings



1

Specifically Designed for **Liquids**

2

Reliable for Peace of Mind

- Compliant with the most demanding **food & beverage regulations** (NSF, FDA, KTW, ACS, WRAS, 1935/2004, DM174)
- **High sealing performance** with the lowest pumping effect on the market (0,2 mm only)
- **High temperature** resistance (+130°C and 10 bar) for tube-to-tube fittings for Ø 4, 6 and 8 mm
- **Compact** product: 20%-40% more compact than competitors
- Proven **automated** process which is camera **controlled**
- 100% leak test control
- Strong quality management system: **ISO 16949 IATF** automotive industry certification
- Products **made in Europe** to ensure a sustainable service

3

Safe for Users' Protection

- **Bisphenol & phthalate-free**
- **No raw material migration** for perfect fluid integrity with our bio-based engineered polymer

4

Safe for Environmental Concern

- **Sustainable** product using bio-based polymer
- Generate **5 times less CO₂** during its life cycle