



Customer Value Proposition:

Parker's PURE food grade hoses enable a clean and safe transfer of a wide variety of foods, beverages, sanitary materials, cosmetics, and pharmaceuticals. Our products are offered in a wide range of constructions and also offer multiple color, pressure, size, and temperature capabilities to meet customer needs. All of our food grade hose and food grade tubes meet government and industry standards to and our hoses are suitable for a variety of markets. They also offer full suction capability and kink resistance to extend their usability and enhanced cover options for convenient and uncomplicated cleaning.



Contact Information:

Parker Hannifin Corporation **Hose Products Division** 30240 Lakeland Blvd. Wickliffe, OH 44092

phone 440 943 5700 fax 440 943 3129 HPD.Support@Support.parker.com

www.parker.com

PURE Cover Options



PURE PURE Standard high grade, UV and ozone resistant, vulcanized rubber, smooth cover.



PURE PRO abrasion resistant, corrugated, non-marking, low friction, easy to clean.



PURE PLUS premium offering, deep corrugation, external PVC helix, crush resistant, most flexible.





PURE**Food**

Series 7620 and 7640 are highquality and flexible delivery and suction hoses. Series 7640 is designed to convey cooking

oils and fat, dairy products, and oily sauces. The tube material for both series consists of premium nitrile (NBR). Series 7620 offers

an antistatic tube allowing for transfer of dry abrasives. We offer multiple cover options to fit your applications individual needs.



PUREFood 7640



Tube	White Nitrile, phthalates free
Temperature	-13°F / +176°F (-25°C / +80°C)
Reinforcement	Synthetic plies, galvanized wire helices
Cover	Smooth, blue, cloth finish. Resistant to abrasion, ageing, ozone and oils.
Sterilization	Refer to Parker's guidelines for cleaning and sanitizing.
ISO 1307	For dimensional tolerances.
Applications	Cooking oils & fat, dairy products, oily sauces

# Part Number	(Ho	se ID	Hose	O.D.	Vacuu	m	Max. Working Pressure		Min. Burst Pressure		kg Weight		Bend Radius	
	in	mm	in	mm	in of Hg	kPa	psi	bar	psi	bar	lbs/ft	kg/m	in	mm
7640-1000	1	25.4	1.46	37	26.5	90	150	10	450	30	0.61	0.91	3.35	85
7640-1500	1.5	38	2	51	26.5	90	150	10	450	30	0.94	1.40	5.91	150
7640-2000	2	51	2.52	64	26.5	90	150	10	450	30	1.21	1.80	8.27	210
7640-3000	3	76	3.58	91	26.5	90	150	10	450	30	2.12	3.17	12.60	320
7640-4000	4	102	4.65	118	26.5	90	150	10	450	30	2.96	4.42	16.93	430



PUREFood 7640P



Tube	White Nitrile, phthalates free
Temperature	-13°F / +176°F (-25°C / +80°C)
Reinforcement	Synthetic plies, galvanized wire helices
Cover	Wide corrugated, blue, low friction material, non-marking when dragged on the floor, easy to clean, glossy. Resistant to abrasion, ageing, ozone, oil and chemicals.
Sterilization	Refer to Parker's guidelines for cleaning and sanitizing.
ISO 1307	For dimensional tolerances.
Applications	Cooking oils & fat, dairy products, oily sauces

# Part Number	Ho	se ID	Hose	O.D.	Vacuu	ım	Max. Working Pressure		Min. Burst Pressure		kg Weight		Bend Radius	
	in	mm	in	mm	in of Hg	kPa	psi	bar	psi	bar	lbs/ft	kg/m	in	mm
7640P-1000	1	25.4	1.46	37	26.5	90	150	10	450	30	0.54	0.81	2.76	70
7640P-1500	1.5	38	2.03	51.5	26.5	90	150	10	450	30	0.82	1.23	3.15	80
7640P-2000	2	51	2.52	66	26.5	90	150	10	450	30	1.27	1.90	3.94	100
7640P-3000	3	76	3.62	91	26.5	90	150	10	450	30	1.95	2.91	5.91	150

WARNING: This product can expose you to chemicals including Titanium Dioxide, which is known to the State of California to cause cancer. For more information go to www.p65warnings.ca.gov.



















PUREBev

Series 7630, 7630P, 7630PL, 7631, and 7632 are high-quality, low permeation, flexible delivery and suction hoses. Collectively, these series are designed to convey

alcohol/spirits (concentration up to 96%), beer, wine, potable water and many other food and beverage applications. Tube materials consist of premium

Butyl. We offer multiple cover options including corrugated and crush resistant options to fit your applications and individual needs.

PURE

PUREBev 7630



Tube	White Butyl, phthalates free
Temperature	-40°F / +248°F (-40°C / +120°C)
Reinforcement	Synthetic plies, galvanized wire helices
Cover	Smooth, red, cloth finish. Resistant to abrasion, ageing and ozone.
Sterilization	Refer to Parker's guidelines for cleaning and sanitizing.
ISO 1307	For dimensional tolerances.
Applications	Beer, wine and consumable liquids

# Part Number		ose D	Ho O.	ose D	Vacuu) m		Vorking ssure		Burst	ि दि दि Weight		Bend Radius	
	in	mm	in	mm	in of Hg	kPa	psi	bar	psi	bar	lbs/ft	kg/m	in	mm
7630-1000	1	25	1.5	40	26.5	90	250	16	750	48	0.69	1.03	3.94	100
7630-1500	1.5	38	2.09	53	26.5	90	250	16	750	48	1.01	1.51	6.10	155
7630-2000	2	51	2.6	66	26.5	90	250	16	750	48	1.31	1.96	8.46	215
7630-2500	2.5	63.5	3.19	81	26.5	90	250	16	750	48	2.02	3.02	10.83	275
7630-3000	3	76	3.7	94	26.5	90	250	16	750	48	2.63	3.92	12.99	330
7630-4000	4	102	4.72	120	26.5	90	250	16	750	48	3.52	5.26	17.72	450

WARNING: This product can expose you to chemicals including Titanium Dioxide, which is known to the State of California to cause cancer. For more information go to www.p65wamings.ca.gov.

















PUREBev 7630P



Tube	White Butyl, phthalates free
Temperature	-40°F / +248°F (-40°C / +120°C)
Reinforcement	, ,
neilliorceilleilt	Synthetic plies, galvanized wire helices
Cover	Wide corrugated, red, low friction material, non-marking when dragged on the floor, easy to clean, glossy. Resistant to abrasion, ageing, ozone, oil and chemicals.
Sterilization	Refer to Parker's guidelines for cleaning and sanitizing.
ISO 1307	For dimensional tolerances.
Applications	Beer, wine and consumable liquids

# Part Number		ose D		ose .D.	Vacuu	ım		Working ssure		Burst	k Wei	□ ⑤ ight	"	Radius
	in	mm	in	mm	in of Hg	kPa	psi	bar	psi	bar	lbs/ft	kg/m	in	mm
7630P-1000	1	25.4	1.5	38	26.5	90	250	16	900	60	0.61	0.91	4.13	105
7630P-1500	1.5	38	2.07	52.5	26.5	90	250	16	900	60	0.92	1.38	4.72	120
7630P-2000	2	51	2.64	67	26.5	90	250	16	900	60	1.48	2.21	5.91	150
7630P-2500	2.5	63.5	3.17	80.5	26.5	90	250	16	900	60	1.87	2.79	7.68	195
7630P-3000	3	76	3.7	94	26.5	90	250	16	900	60	2.35	3.51	8.86	225

WARNING: This product can expose you to chemicals including Titanium Dioxide, which is known to the State of California to cause cancer. For more information go to www.p65warnings.ca.gov.



















PUREBev 7630PL



Tube	Vhite Butyl, phthalates free							
Temperature	-13°F / +248°F (-25°C / +120°C)							
Reinforcement	Synthetic plies, thermoplastic wire helices							
Cover	Deeply corrugated, red smooth rubber, red outer thermoplastic helix nested within the rubber cover. Resistant to abrasion, ageing, and ozone.							
Sterilization	Refer to Parker's guidelines for cleaning and sanitizing.							
ISO 1307	For dimensional tolerances.							
Applications	Beer, wine and consumable liquids							

# Part Number		ose ID	Vacuu	Jim		Vorking ssure	Min. Pres	Burst	kg Weight		Bend Radius	
	in	mm	in of Hg	kPa	psi	bar	psi	bar	lbs/ft	kg/m	in	mm
7630PL-1500	1.5	38	26.5	90	150	10	450	30	0.94	1.40	3.15	80
7630PL-2000	2	51	26.5	90	150	10	450	30	1.24	1.84	3.94	100
7630PL-2500	2.5	63.5	26.5	90	150	10	450	30	1.48	2.20	5.12	130
7630PL-3000	3	76	26.5	90	150	10	450	30	1.90	2.83	5.91	150
7630PL-4000	4	102	26.5	90	150	10	450	30	2.46	3.66	7.87	200



WARNING: This product can expose you to chemicals including Titanium Dioxide, which is known to the State of California to cause cancer. For more information go to www.p65warnings.ca.gov.



Green PVC Banding Coil Series 7630CL

7630CL-1	to be used with 7630PL hose sizes 1.5" - 2.5"
7630CL-2	to be used with 7630PL hose sizes 3" - 4"

















PUREBev 7632



Tube	White Butyl, phthalates free
Temperature	-40°F / +248°F (-40°C / +120°C)
Reinforcement	Synthetic plies, crush-resistant, rust-proof, monofilament helix
Cover	Smooth, purple, cloth finish. Resistant to abrasion, ageing and ozone.
Sterilization	Refer to Parker's guidelines for cleaning and sanitizing.
ISO 1307	For dimensional tolerances.
Applications	Beer, wine and consumable liquids

# Part Number		ose ID	Ho: O.I		Vacuum		Max. Working Pressure		Min. Burst Pressure		【 【版 g] Weight		Bend Radius	
	in	mm	in	mm	in of Hg	kPa	psi	bar	psi	bar	lbs/ft	kg/m	in	mm
7632-1000	1	25	1.61	41	20.4	69	250	16	1,000	64	0.66	0.98	4.52	115
7632-1500	1.5	38	2.16	55	20.4	69	250	16	1,000	64	1.00	1.49	7.08	180
7632-2000	2	51	2.67	68	20.4	69	250	16	1,000	64	1.24	1.85	9.84	250
7632-2500	2.5	63.5	3.23	82	20.4	69	250	16	1,000	64	1.86	2.77	12.59	320
7632-3000	3	76	3.78	96	20.4	69	250	16	1,000	64	2.17	3.23	15.35	390

WARNING: This product can expose you to chemicals including Titanium Dioxide, which is known to the State of California to cause cancer. For more information go to www.p65warnings.ca.gov.

















PURE**Spirits**

Series 7650P is high-quality, low permeation, flexible delivery and suction hoses. Collectively, these series are designed to convey alcohol/spirits (concentration


up to 96%), beer, wine, potable water and many other food and beverage applications. Tube materials consist of premium UHMWPE materials. We offer

multiple cover options including corrugated and crush resistant options to fit your applications and individual needs.



PURESpirits SERIES 76

PURESpirits 7650P



# Part Number		ose D	Ho O.		Vacuum		Max. Working Pressure		Min. Burst Pressure		kg Weight		Bend Radius	
	in	mm	in	mm	in of Hg	kPa	psi	bar	psi	bar	lbs/ft	kg/m	in	mm
7650P-0750	.75	19	1.25	31.5	26.5	90	150	10	450	30	0.60	0.89	4.33	110
7650P-1000	1	25.4	1.46	37	26.5	90	150	10	450	30	0.54	0.80	3.94	100
7650P-1500	1.5	38	1.97	50	26.5	90	150	10	450	30	0.76	1.14	5.91	150
7650P-2000	2	51	2.56	65	26.5	90	150	10	450	30	1.21	1.81	7.87	200
7650P-3000	3	76	3.58	91	26.5	90	150	10	450	30	1.88	2.81	13.78	350
7650P-4000	4	102	4.61	117	26.5	90	150	10	450	30	2.46	3.67	19.69	500



WARNING: This product can expose you to chemicals including Titanium Dioxide, which is known to the State of California to cause cancer. For more information go to www.p65warnings.ca.gov.

All PURESpirits hoses comply with the following standards:

















PURE**PTFE**

Series 7660 is comprised of highquality delivery and suction hoses for both chemicals and solvents. This series is designed to convey various chemicals, cosmetics, foods, and pharmaceutical

materials. Not intended for use with chlorine trifluoride, chlorine/fluoride gas, human fluids, liquid alkalis, and oxygen difluoride. Tube material consists of premium PTFE

which has exceptional temperature tolerance. We offer multiple cover options to fit your applications individual needs.

PURE**PTFE 7660**



Tube	Clear PTFE
Temperature	-40°F / +302°F (-40°C / +150°C)
Reinforcement	Synthetic plies, stainless steel wire helices, a/s wire to discharge static electricity.
Cover	Smooth, white cloth finish. Resistant to abrasion, ageing and ozone.
Sterilization	Refer to Parker's guidelines for cleaning and sanitizing.
ISO 1307	For dimensional tolerances.
Applications	Various chemicals, cosmetics, pharmaceutical materials

# Part Number	Ho II		Hose O.D.		Vacuum		Max. Working Pressure		Min. Burst Pressure		版g Weight		Send Radius	
	in	mm	in	mm	in of Hg	kPa	psi	bar	psi	bar	lbs/ft	kg/m	in	mm
7660-0500	.50	13	1	25	26.5	90	250	16	1000	64	0.34	0.50	2.95	75
7660-0750	.75	19	1.22	31	26.5	90	250	16	1000	64	0.34	0.51	4.33	110
7660-1000	1	25	1.46	37	26.5	90	250	16	1000	64	0.44	0.66	5.91	150
7660-1500	1.5	38	2	51	26.5	90	250	16	1000	64	0.74	1.11	9.45	240
7660-2000	2	50	2.6	64	26.5	90	250	16	1000	64	0.90	1.35	12.6	320



WARNING: This product can expose you to chemicals including Titanium Dioxide, which is known to the State of California to cause cancer. For more information go to www.p65warnings.ca.gov.

PUREPTFE 7660 hose complies with the following standards: FDA



















PURE**PTFE 7660P**



Tube	Black PTFE, conductive
Temperature	-40°F / +302°F (-40°C / +150°C)
Reinforcement	Synthetic plies, stainless steel wire helices, a/s wire to discharge static electricity.
Cover	Corrugated, white with conductive chips, low friction material, non-marking when dragged on the floor, easy to clean, glossy. Resistant to oil, chemical, abrasion, ageing and ozone. Meets FDA 21 cfr 177.1520.
Sterilization	Refer to Parker's guidelines for cleaning and sanitizing.
EN12115	
Applications	Various chemicals, cosmetics, pharmaceutical materials

# Part Number		ose D	Hose O.D.		Vacuum		Max. Working Pressure		Min. Burst Pressure		kg Weight		Bend Radius	
	in	mm	in	mm	in of Hg	kPa	psi	bar	psi	bar	lbs/ft	kg/m	in	mm
7660P-0500	.50	13	1	25	26.5	90	150	10	600	40	0.33	0.49	2.76	70
7660P-0750	.75	19	1.22	31	26.5	90	150	10	600	40	0.43	0.64	3.94	100
7660P-1000	1	25	1.46	37	26.5	90	150	10	600	40	0.53	0.79	5.12	130
7660P-1500	1.5	38	2	51	26.5	90	150	10	600	40	0.83	1.24	7.48	190
7660P-2000	2	50	2.6	64	26.5	90	150	10	600	40	1.23	1.84	9.84	250

WARNING: This product can expose you to chemicals including Titanium Dioxide, which is known to the State of California to cause cancer. For more information go to www.p65warnings.ca.gov.

PUREPTFE 7660P hose complies with the following standards: FDA CE



















PUREWash

Washdown hose is used in virtually every type of food and beverage processing plant.
Sanitation of equipment and work areas is critical in packing houses, hot processing plants, breweries, dairies, wineries, and general industrial applications. Cleaning and purification practices require a commitment to preventative maintenance. This in turn extends the life of equipment and productivity. Devoted to developing products to support

our customers in these critical applications and to complement our food hose line, Parker has developed PUREWash hoses, 7680 and 7685, replacing our existing washdown hoses.

Additional Features include:

 FDA compliant tube (7680 ONLY)
 (not to be used in food contact/transfer)

- Enhanced printed layline
- Non-marking covers
- Additional cover colors for a cleaner look
- Compatible with Parkrimp crimpers or variable crimpers.
 Please refer to Crimpsource for specifications.

PURE PU

PUREWash 7680



Tube	White EPDM; FDA Compliant
lube	Willie Li Divi, i DA Compliant
Temperature	-40°F / +212°F (-40°C / +100°C)
Reinforcement	Multiple textile plies
Cover	White (WHT) or Blue (BLU) EPDM; smooth finish.
Sterilization	Refer to Parker's guidelines for cleaning and sanitizing.
Applications	Food & beverage processing plants, equipment sanitation, preventative maintenance

# Part Number			Reinf Plies	Hose O.D.		Approximate Weight		Minimum Bend Radius			mum : WP	Perm Cplg Rec	Std Pack Qty
	in	mm		in	mm	lbs/ft	kg/ft	in	mm	psi	bar		ft
7680-8-WHT-RL	.50	12.7	4	0.875	22.2	0.25	0.11	5	127	300	20.7	HY	500
7680-8-BLU-RL	.50	12.7	4	0.875	22.2	0.25	0.11	5	127	300	20.7	HY	500
7680-12-WHT-RL	.75	19.1	4	1.156	29.4	0.37	0.17	6	152	300	20.7	HY	400
7680-12-WHT-BX	.75	19.1	4	1.156	29.4	0.38	0.17	6	152	300	20.7	HY	50
7680-12-BLU-RL	.75	19.1	4	1.156	29.4	0.38	0.17	6	152	300	20.7	HY	400
7680-12-BLU-BX	.75	19.1	4	1.156	29.4	0.38	0.17	6	152	300	20.7	HY	50
7680-16-WHT-RL	1	25.4	4	1.438	36.5	0.52	0.24	8	203	300	20.7	HY	300
7680-16-BLU-RL	1	25.4	4	1.438	36.5	0.53	0.24	8	203	300	20.7	HY	300



WARNING: This product can expose you to chemicals including Titanium Dioxide, which is known to the State of California to cause cancer. For more information go to www.p65warnings.ca.gov.


PUREWash 7685



Tube	Black EPDM
Temperature	-40°F / +250°F (-40°C / +121°C)
Reinforcement	Multiple aramid plies
Cover	Gray and Yellow; smooth finish.
Sterilization	Refer to Parker's guidelines for cleaning and sanitizing.
Applications	Hot water, mild chemicals. Breweries, dairies, food/poultry processing plants, general industrial

# Part Number			Reinf Plies		Hose O.D.		Approximate Weight		Minimum Bend Radius		mum	Perm Cplg Rec	Std Pack Qty
	in	mm		in	mm	lbs/ft	kg/ft	in	mm	psi	bar		ft
7685-6-GRA-RL	.375	9.5	4	0.765	19.43	0.21	0.31	4	102	1500	103	HY	500
7685-6-YEL-RL	.375	9.5	4	0.765	19.43	0.21	0.31	4	102	1500	103	HY	500

WARNING: This product can expose you to chemicals including Titanium Dioxide, which is known to the State of California to cause cancer. For more information go to www.p65warnings.ca.gov.



Parker Fluid Connectors Group North American Divisions & Distribution Service Centers

Your complete source for quality tube fittings, hose & hose fittings, brass & composite fittings, quick-disconnect couplings, valves, and assembly tools, locally available from a worldwide network of authorized distributors.

Fittings:

Available in inch and metric sizes covering SAE, BSP, DIN, GAZ, JIS, and ISO thread configurations, manufactured from steel, stainless steel, brass, aluminum, nylon, and thermoplastic.

Hose, Tubing, and Bundles:

Available in a wide variety of sizes and materials including rubber, wire-reinforced, thermoplastic, hybrid and custom compounds.

Worldwide Availability:

Parker operates Fluid Connectors manufacturing locations and sales offices throughout North America, South America, Europe, and Asia-Pacific.

For information, call toll-free:

1-800-C-PARKER (1-800-272-7537)

North American Divisions

Hose Products Division

Wickliffe, OH phone 440 943 5700 fax 440 943 3129

Fluid System Connectors Division

Otsego, MI phone 269 694 9411 fax 269 694 4614

Parflex Division

Ravenna, OH phone 330 296 2871 fax 330 296 8433

Quick Coupling Division

Minneapolis, MN phone 763 544 7781 fax 763 544 3418

Tube Fittings Division

Columbus, OH phone 614 279 7070 fax 614 279 7685

Distribution Service Centers

Buena Park, CA

phone 714 522 8840 fax 714 994 1183

Louisville, KY

phone 502 937 1322 fax 502 937 4180

Portland, OR

phone 503 283 1020 fax 503 283 2201

Toledo, OH

phone 419 878 7000 fax 419 878 7001 fax 419 878 7420 (FCG Kit Operations)

Canada Milton, ONT

phone 905 693 3000 fax 905 876 1958 (Contact Milton for other Service Center locations.)

© 2023 Parker Hannifin Corporation



05/2023



Parker Hannifin Corporation

Hose Products Division
30240 Lakeland Blvd.

Wickliffe, OH 44092
phone 440 943 5700
fax 440 943 3129
www.parker.com/safehose
HPD.Support@Support.parker.com