

# SALES TIPS

## Stainless Steel Couplings



1

### Resistant for Demanding Applications

- The best in class stainless steel (316L) available to resist to internal and external **aggressive fluids**
- **High temperature** resistance (up to +200 °C) and large **chemical** compatibility thanks to FKM seals
- Ideal for **food**, **chemical** and **medical** process applications

2

### Reliable for Peace of Mind

- **Proven technologies** designed by in-house German Engineers
- Leak and function **test controls**
- Products **made in Europe**, to ensure a sustainable service