

SALES TIPS

LF 3600 Push-In Fittings



1

Robust for Demanding Applications

- **Full metal design** in nickel-plated brass, perfect to resist to mechanical shocks and external aggressive environments
- Spark resistance, suitable for **in-plant automotive** applications
- High **vibration & pressure resistance**, up to 30 bar with the collet gripping technology, meeting **transportation & railway industries** requirements
- Large range of **temperatures** (-25° to +150°C) and **media** thanks to the FKM seal

2

Reliable for Peace of Mind

- **FDA chemical nickel-plated brass** conforms to **food process** requirements and other severe applications
- Proven **automated** process which is **camera controlled**
- 100% leak test control
- **Quality Management** system that follows ISO IATF 16949 automotive industry requirements
- Products **made in Europe** to ensure a sustainable service